# KERN **328-06**

Milligram weights, F1, 50 mg, Platelet, stainless steel polished



## Category

| | |
|---|---|
| Brand | KERN |
| Product category | Individual weight |
| Product group | OIML F1 |
| Product family | 328 |

## Measuring System

| | |
|---|---|
| Test weight - nominal value | 50 mg |
| Test weight - volume uncertainty ($cm^3$) | 0,0001 |
| Weight OIML class | F1 |
| Test weight - volume ($cm^3$) | 0,0058 |
| Permissible tolerance according to OIML (+/-) | 0,04 mg |
| OIML-compliant | ✓ |
| Test weight - Density [Min] (OIML) | 3400 |
| Test weight - Density [Max] (OIML) | 100000 |
| Test weight - Density ($kg/m^3$) | 7960 |
| Test weight - Density uncertainty ($kg/m^3$) | 170 |

## Construction

| | |
|---|---|
| Shape weight | Platelet |
| Dimensions weight (W×D×H) | 7,5×6×3 mm |
| Material | stainless steel polished |
| Adjustment method | Filing |

## Services (optional)

| | |
|---|---|
| Article number for DAkkS calibration | 962-456 |
| Article number for guaranteed plus-deviation | 921-456 |

## Packing & Shipping

| | |
|---|---|
| Delivery time | 1 d |
| Dimensions packaging (W×D×H) | 7,5×6×3 mm |
| Shipping method | Parcel service |
| Net weight approx. | 0,05 kg |
| Gross weight approx. | 0,05 kg |
| Shipping weight | 0,1 kg |
| Shipping volume weight | 0,1 kg |

## Optional cases

| | |
|---|---|
| Case - Plastic article number | 347-009-400 |
| Case - Aluminium article number | 317-009-600 |
| Case - Wood article number | 338-090-200 |

## Product information

| | |
|---|---|
| GTIN/EAN number | 4045761240360 |
| Trade number | 84239090 |
| REACH classification | no prohibited substances |

## Pictograms

### STANDARD

1 DAY

### OPTION

DAkkS