

# Combi empty\_2



Products   Low Voltage Products and Systems   Industrial Plugs and Sockets   Adaptors

Products   Low Voltage Products and Systems   Industrial Plugs and Sockets   Modular Combination Boxes

## General Information

<b>Extended Product Type:</b>	Combi empty_2
<b>Product ID:</b>	2CMA101659R1000
<b>EAN:</b>	7392696016599
<b>Catalog Description:</b>	Modular Combi Plastic enclosure
<b>Long Description:</b>	Modular Combi accessories Combi empty_2

## Additional Information

<b>Additional Information:</b>	Cable entry,4 knock-outs at the top,suitable for 2xØ40mm and 2xØ25mm,at the bottom 3xØ47mm
<b>Cable Entry Position:</b>	Cable entry,4 knock-outs at the top,suitable for 2xØ40mm and 2xØ25mm,at the bottom 3xØ47mm
<b>Color:</b>	Grey
<b>Country of Origin:</b>	Czech Republic (CZ)
<b>Customs Tariff Number:</b>	85389099
<b>Data Sheet, Technical Information:</b>	2CMC000024M0000
<b>Declaration:</b>	2CMC700005D0004
<b>Declaration of Conformity - CE:</b>	2CMC700005D0004
<b>Degree of Protection:</b>	IP44
<b>EAN:</b>	7392696016599
<b>ETIM 4:</b>	EC000379 - CEE socket outlet combination
<b>ETIM 5:</b>	EC000261 - Switchgear cabinet (empty)
<b>ETIM 6:</b>	EC000261 - Enclosure/switchgear cabinet (empty)
<b>Enclosure Material:</b>	Plastic
<b>Environmental Information:</b>	2CMC700001D0002
<b>Gross Weight:</b>	3.32 kg
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Instructions and Manuals:</b>	2CMC711001M0201
<b>Invoice Description:</b>	Ind.P-S_Combi empty_2
<b>Minimum Order Quantity:</b>	1 piece
<b>Number of Poles:</b>	5
<b>Package Level 1 Gross Weight:</b>	3.32 kg
<b>Package Level 1 Height:</b>	490 mm
<b>Package Level 1 Length:</b>	270 mm
<b>Package Level 1 Units:</b>	1 piece
<b>Package Level 1 Width:</b>	210 mm
<b>Product Main Type:</b>	Accessory
<b>Product Name:</b>	Industrial Plug and Socket Accessorie
<b>Product Net Depth:</b>	358 mm
<b>Product Net Height:</b>	124 mm
<b>Product Net Length:</b>	358 mm
<b>Product Net Weight:</b>	3.32 kg
<b>Product Net Width:</b>	251 mm
<b>Protection Type:</b>	Splashproof
<b>Rated Current (I<sub>n</sub>):</b>	32 A
<b>Rated Voltage (U<sub>r</sub>):</b>	Optional V
<b>Selling Unit of Measure:</b>	piece
<b>Short Description:</b>	Modular Combi Plastic enclosure
<b>Size:</b>	124x124x16
<b>UNSPSC:</b>	39120000
<b>Clock Position Of Grounding Contact:</b>	6 hour

