KERN **ORA 3AA**

Refractive index measurement for laboratories and the industry

Category

Brand	Optics
Product categoriy	Refractometer
Product group	Analogue refractometer
Product family	ORA-AL

Measuring System

Measurement temperature [Min] (°C)	10 °C
Measurement temperature [Max] (°C)	30 °C
Measuring method	Light refraction
Measuring range Brix [Min]	0 %
Scales	Brix Stammwürze (Bier)
Measuring ranges	0 % - 32 % 1,000 SG Wort - 1,130 SG Wort
Readabilites [d]	0,2 % 0,001 SG Wort
Readout Brix	0,2 %
Automatic temperature compensation (ATC)	✓
Measuring range original hopped wort (specific gravity) [Min]	1,000
Measuring range original hopped wort (specific gravity) [Max]	1,130
Readout original hopped wort (specific gravity)	0,001
Scale original hopped wort (specific gravity)	✓
Appropriate calibration liquid	0 % (distilled water)
Measuring range Brix [Max]	32 %
Brix scale	✓
Area of application	Beer

Construction

Dimension (W×D×H)	198×40×40 mm
Refractometer type	Handheld refractometer
Scale - Display type	Analogue
Material prism	ZLaF3 lanthanum flint glass nd=1.85544

Functions

IP protection - complete device	-

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Services (optional)

Article number for factory calibration	961-290

Packing & Shipping

Dimensions transport container (W×D×H)	205×75×55 mm
Delivery time	1 d
Dimensions packaging (W×D×H)	215×94×65 mm
Shipping method	Parcel service
Net weight approx.	0,30 kg
Gross weight approx.	0,35 kg
Shipping weight	0,32 kg

Product information

GTIN/EAN number	4045761263390
REACH classification	no prohibited substances

Pictograms

STANDARD