



Technical Specification

25m + 3m Reverse Open Reel OMU2513FL3IP




Features

- » Innovative reverse reel, with weatherproof socket
- » Safety thermal cut-out
- » Power LED indicator
- » IP54 rated weatherproof socket
- » Compatible with wall mount bracket

Description

This innovative design allows you to wall mount the extension reel near the wall power outlet and extend the power socket closer to the required area. The drum's construction provides reliable protection when in use, transported or stored. The compact design is perfect for the home, garden and light industrial use. Using highly visible green cable, this 'reverse' extension reel provides an IP54 rated weatherproof 13 amp socket outlet. The drum includes an LED indicator, and has a built-in safety thermal cut-out for protection against overloading when fully reeled. Optional wall bracket available.

Line Diagrams



Technical Specifications

Standards	BS EN 61242. ASTA Approved
Maximum Load	720W/240V - Fully Wound 3120W/240V - Fully Unwound
Switch	Double Pole
Cable length	25+3m
Cable Size	Cable Size - 1.25mm ² (H05VV-F)



Lic 940



Product Information

Part No	OMU2513FL3IP	Qty	1
Type	Reverse Reel with Pull Out Socket	Shipping Carton Info (m)	H:0.27 x W:0.26 x D:0.27
Cable Type	PVC	CBM (m ³)	0.019
Cable Length (m)	25+3m	G.W (kg)	4.5
Amp	13	EAN Barcode	5015056526553
Product Dimensions (cm)	H:24.7 x W:22 x D:21	ITF Barcode	05015056526652

Product Range

Product Image	Cat No	Description	Length (m)	Sockets	Amps
	CMU10134SL	Cassette Reel	10m	4 Sockets	13
	HMU15134SL	Case Reel	15m	4 Sockets	13
	OMU25134SL	Open Reel	25m	4 Sockets	13
	OLU50134SL	Open Reel	50m	4 Sockets	13
	OTLU40134SL	Heavy Duty Metal Open	40m	4 Sockets	13
	OMU2513FL3IP	Reverse Open Reel	25+3m	1 Socket	13
	OATRU3013FL3IP	Anti-Twist Reverse Reel	30+3m	1 IP54 Socket, + LED	13
	OATFU30134SL	Anti-Twist Fixed Socket	30m	4 Sockets, Switch + LED	13
	OMU25132USL	Open Reel with USB Charging	25m	2 Sockets, Switched + USB	13

Masterplug are proud to offer a 5 year warranty on its range of Pro-XT portable power products from the date of purchase.

Please see our website www.masterplug-proxt.com for more details.

UK Sales & Distribution Centre

Luceco plc

Stafford Park 1, Telford, Shropshire, England, TF3 3BD

Tel: +44 (0) 1952 238 100 Fax: +44 (0) 1952 238 180

Email: sales@masterplug.com

www.masterplug-proxt.com

Tech Help Line: (UK) 03300 249 279
(Non UK) +44(0) 1952 238 100



**POWER
AT WORK**

