
RS PRO Red LED Indicator Lamp

RS Stock No.: 800-979



Features

- Signalling LED (red).
- Supply voltage: A1-A2, AC 230 V, A1-A3, AC/DC 24 V
- Operating temperature -20 °C .. +55 °C (-4 °F .. 131 °F)..
- M3 screw with clamp terminals.
- Units are delivered as components and configured by the user.


RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description


- *Independent switch units designed for flexible controlling and switching of power circuits.*
- *"Do It Yourself" = it is possible to "click into" different types of switches and signalling units into the basic module.*
- *It is possible to place up to two units into one MODULE (for example 2x switch, 2x signalling lights or combinations) = saves space in switchboard panels.*
- *1-MODULE (90 x 17.6 x 64 mm/3.5˝ x 0.7˝ x 2.5˝), DIN rail mounting.*
- *Dimensions of the unit: 21 x 15 x 14 mm (0.83˝ x 0.59˝ x 0.55˝).*

Connection






Connection of signaling light



Other information



Examples of mounting

