



### Tamper-evident security labelling, thermal transfer

#### Helatag 951 (Silver, Transparent), 2 parts

These labels are primarily used for tamper-proof type label applications in the automotive and electrical industries.

They are ideally suited for labelling flat surfaces, e.g. on vehicle frames and can be used as a replacement for conventional aluminium plates.


The transparent protective laminate guarantees good resistance to dirt and abrasion and can be easily applied by hand.

#### Features and benefits

- 2-part label, delivered on reel together with the protective label
- Designed for highly visible and rugged identification on trucks and trailers
- Tamper-evident, when pulled off a checkered pattern will be visible as evident
- High durability in outside use
- Meets requirements of the KBA (Kraftfahrtbundesamt [German Federal Motor Transport Authority])
- Thickness of 951A label 36 µm and 951B laminate 25 µm
- Particularly suitable as type label for vehicles



Type plate of an HGV trailer with protective laminate.




The printed silver type plate (Mat. 951A) is protected by the transparent laminate (Mat. 951B).



**Tested according to German Federal Motor Transport Authority (KBA) technical bulletin 412-205 (Testing of factory plates made of foil and the affixing thereof with adhesive).**

<b>MATERIAL</b>	Type 951, Polyester (PET), silver (SR) and Polyester (PET), transparent (CL)
<b>Operating Temperature</b>	-40 °C to +150 °C
<b>Curing Temperature</b>	from 0 °C (label), from +4 °C (laminate)
<b>Adhesive</b>	Acrylic
<b>Thickness of Foil</b>	36 µm, 25 µm
<b>Chem. Material Properties</b>	Excellent resistance to water, alcohol, most oils, greases, fuel, aliphatic solvents, weak acids, salts and alkalis.
<b>Recommended Ribbon Type</b>	TT822OUT
<b>Thermal Transfer Printer</b>	TT430, TT4030



TYPE	Width (W)	Height (H)	Width of Liner (WL)	Labels per Row	Pack Cont.	Colour	Article-No.
<b>TAG25.4-12.7TD1-951 SET</b>	25.4	12.7	31.5	1 pc.	1,000 pcs.	Silver (SR)	596-44951
<b>TAG50.8-25.4TD1-951 SET</b>	50.8	25.4	56.8	1 pc.	1,000 pcs.	Silver (SR)	596-43951
<b>TAG63.5-50.8TD1-951 SET</b>	63.5	50.8	69.5	1 pc.	500 pcs.	Silver (SR)	596-42951
<b>TAG101-74TD1-951 SET</b>	101.6	74.0	107.0	1 pc.	250 pcs.	Silver (SR)	596-41951
<b>TAG101-160TD1-951 SET</b>	101.6	160.0	105.8	1 pc.	250 pcs.	Silver (SR)	596-40951

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.



For product specific approvals and specifications please refer to the Appendix.