

# POLYAMIDE (PA) FLEXIBLE TUBING

✉ Email    🖨 Print



Tried-and-tested for industrial or vehicle applications, PA tubing guarantees excellent durability due to its stable long-term mechanical properties. Special grade of semi-rigid polyamide manufactured according to our Eco-Design approach.

**PART NUMBER:**  
1100P14 00

**TUBING MATERIAL:**  
PA

**TUBE I.D. (MM):**  
12

**TUBE O.D. (MM):**  
14

**COLOR:**  
NATURAL

**LENGTH (M):**  
100

[Reset Attributes](#)

WHERE TO BUY

<b>PRODUCT OVERVIEW</b>	<b>-</b>
<b>TECH SPECIFICATIONS</b>	<b>+</b>

[Print Tech Specifications](#)

## PERFORMANCE CHARACTERISTICS

### MAXIMUM PRESSURE (BARG)

50

### MINIMUM WORKING TEMPERATURE (°C)

-40

### MAXIMUM WORKING TEMPERATURE (C)

100

### VACUUM RATING (MM OF HG)

755

### WEIGHT (KG/PACKAGE)

7.2

### MAXIMUM BEND RADIUS (MM)

116

### NUMBER OF TUBES

1

## APPLICATION

Packaging, Tooling, Compressed Air, Motion Technologies, Robotics, Industrial Machinery

## MEDIA

Semi-Rigid PA: Compressed air, other fluids /Rigid PA:  
Compressed air,lubricants, other fluids

## CERTIFICATES

Industrial: DI: 2002/95/EC (RoHS), 2011/65/EC; DI: 97/23/EC (PED); RG: 1907/2006 (REACH)/Transportation: Chemical performance and resistance tested according to DIN 74324 -1 / DIN 73378 / ISO 7739

[Print Tech Specifications](#)

<b>PRODUCT SUPPORT</b>	<b>+</b>
------------------------	----------

### RECOMMENDED



filters



Stainless Steel Non-Return Valves



Pneumatic Sensor Fittings



Pneumatic Pilot Non-Return Valve

### CONTACT US

#### Parker Hannifin Manufacturing France SAS

Fluid System Connectors Division Europe  
Parc Alcyone - Bat. D  
1 rue André et Yvonne Meynier - CS 46911  
35069 Rennes Cedex France

#### Phone

Phone: +33 (0) 2-99-25-55-00



EMAIL PARKER

### Parker Hannifin +

Products

About Parker

Investors

Community

Careers

### Global Operations +

Divisions

Sales Companies

Worldwide Locations

Distribution Network

ParkerStore™ Network

### Company Information +