

# 30MM PUSH BUTTON FULL GUARD

Local distributor code: 387211266

9001KR1U

EAN Code: 3389110911664

## Main

Range of product	Harmony 9001K
Product or component type	Head for push-button
Device short name	9001K
Operator profile	flush, unmarked
Operator additional information	Metal guard

# Complementary

Mounting diameter	30 mm
Shape of signaling unit head	Round
Type of operator	spring return
Net weight	0.087 kg
Bezel material	Metal
Cap/operator or lens colour	7 colours choice
Operator profile	Flush
Type of operator	Spring return
Contacts type and composition	Without contact block

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.500 cm
Package 1 Width	5.500 cm
Package 1 Length	5.000 cm
Package 1 Weight	104.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	24
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.622 kg

# **Logistical informations**

Country of origin FR

# **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

#### **Use Better**

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Ae0c4eb9-0bfb-40a4-851f-5c619fbe777d
REACh Regulation	REACh Declaration

#### **Use Again**


○ Repack and remanufacture						
Take-back	No					
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins					

# **Product datasheet**

# 9001KR1U

# **Dimensions Drawings**

## **Dimensions**




## 9001KR1U

## Mounting and Clearance

## **Contact Block Mounting Position**


#### Top and Rear views



- (1) It is possible to mount up to 3 levels of contacts blocks (maximum of 6 contacts blocks)
- (2) Operator
- (3) Locating notch
- (4) Side 1
- (5) Side 2

## Panel Cut-Out


#### Clearance




Legend plate	a min.		b min.	
	mm	in.	mm	in.
9001KN2••	57.2	2.25	44.5	1.75
9001KN3••	57.2	2.25	50.8	2.00

#### **Individual Cut-outs Details**

#### 2 alternatives





Offer Marketing Illustration

#### **Product benefits / Features**

## **Technical Benefits**

## Harmony 9001K



Offer Marketing Illustration

#### **Product benefits / Features**



Image of product / Alternate images

## **Alternative**















