

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0347920041](#)  
**Status:** **Active**  
**Overview:** [Mini50 Connection Systems](#)  
**Description:** Mini50 Unsealed Vertical Header, Single Row, 4 Circuit, Polarization Option B, Gray, Tray

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification AS-34791-020-FR-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-31301-440 (PDF)</a>
<a href="#">Product Specification PS-34791-020-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification AS-34791-020 (PDF)</a>	<a href="#">Product Literature (PDF)</a>
<a href="#">Application Specification AS-34791-020-CH-001 (PDF)</a>	

**General**

Product Family	PCB Headers
Series	<a href="#">34792</a>
Application	Power, Signal, Wire-to-Board
Overview	<a href="#">Mini50 Connection Systems</a>
Product Literature Order No	987650-5442
Product Name	Mini50
UPC	884982492820

**Physical**


Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Gray
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin over Nickel
Material - Plating Termination	Tin over Nickel
Material - Resin	Polyester Alloy
Net Weight	1.057/g
Number of Rows	1
Orientation	Vertical
PC Tail Length	2.90mm
PCB Locator	Yes
Packaging Type	Tray
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

**Electrical**

Current - Maximum per Contact	4.0A
Voltage - Maximum	500V DC

**Material Info**

**Reference - Drawing Numbers**



*Series image - Reference only*

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/61/2018 (27 June 2018)

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Not Relevant

Compliant

Not Contained

**Search Parts in this Series**

[34792 Series](#)

**Mates With**

[34791 Mini50 Unsealed Single Row Receptacle](#)

Application Specification

Packaging Specification

Product Specification

AS-34791-020, AS-34791-020-CH-001, AS-34791-020-  
FR-001

PK-31301-440

PS-34791-020-001

This document was generated on 09/20/2018

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**