Technical datasheet



BB 1507 FLH

Uninsulated Tab Female + Male, Reel, 0.5-1.0mm2, 6.3x0.8mm

CE

Product Properties:

Model	Bushing
Max. current (Imax)	10 A
Insulation	Not isolated
Colour insulation	Other
With cam clamp	No
With tap spreader	Yes
Material insulation	Other
Operating temperature	-10-110 °C
Material	Brass
Neck type	Open barrel crimp

Dimensions:

E	7.7 mm
T	2.2 mm
L	19 mm
W	7.7 mm
MOQ	1300 .
Unit	pcs
Nominal cross section	0.5-1 mm²
Plug dimensions	Flat 6.3x0.8 mm

Approvals:

Approved according to CE	Yes

Compliance:

CA Proposition 65	In compliance
Conflict Minerals	Contain "Tin"
Extended Minerals	Contain "Copper"
Iron and Steel Sanction	Contain no Iron or Steel
PFAS	No PFAS
POPs	In compliance
REACH	No SVHC (247 Subs. 21 Jan 2025)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
US TSCA	No (5 PBT Subs, Feb 2021)
ECCN (EU)	No CLASS
ECCN (US)	EAR99

Other information:

ETIM-Class	EC000516 - Round or flat plug/receptacle
ETIM-Release	10.0
Trademark	NEMIQ
Product Group	Uninsulated Tab female + male - Reel
Search Description	JST, 36921800 , SPB-1.0T-250N-S
Alternative SKU	BB1507FLH

Logistic information:

Barcode	733117615007
Country of origin	BE
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	1300 .
Stock code	BB 1507 FLH
Taric code	85369010
Unit	pcs

*We reserve the right to make technical changes and disclaim any typographical errors.

Nelco Contact AB - Daléns Gata 7, 195 61 Arlandastad, Sweden - Tel. +46 (0)8 754 70 40 - order@nelco.se - www.nelco.se