Product information

82 02 150

KNIPEX TwinGrip®

Front and side gripping pliers

- Gripping, tightening and loosening screws with worn heads and threads
- Unique combination: Front grip and side grip function, box joint, push button adjustment
- High-grip front jaw with robust teeth and high gear ratio at the tip of the mouth

- Small and handy – also suitable for more delicate work
- Very slim pliers let you work even in confined installation spaces with a narrow turning zone for fast results
- Large front and side gripping capacities: for diameters and width across flats 3 – 16 mm
- Reliable, frontal gripping of flat workpieces up to 6 mm thanks to three-point system
- Three-way adjustable slip joint with push button adjustment for precise alteration of gripping capacity
- Optimised geometry of the side jaw design: with locking effect for maximum grip when loosening and tightening
- Pinch stop reduces the risk of crushed fingers
- Durable and resilient thanks to robust box joint

General	
Part No.	82 02 150
EAN	4003773089360
pliers	grey atramentized
head	polished
handles	with comfort handles
Weight	278 g
Dimensions	150 x 45 x 18 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Capacities for pipes (diameter)	Ø 1/8 – 5/8 Inch
Capacities for pipes (diameter)	Ø 3 – 16 mm
Capacities for nuts	3 – 16 mm
Capacities for nuts	1/8 – 5/8 Inch

technical change and errors excepted

KNIPEX

KNIPEX