Pushing Performance

# Han-Eco 16B-HSE-for SL-M40-glanded

| | |
|---|---|
| Part number | 19 43 116 0548 |
| Specification | Han-Eco 16B-HSE-for SL-M40-glanded |
| HARTING eCatalogue | https://b2b.harting.com/19431160548 |

## Identification

| | |
|---|---|
| Category | Hoods/Housings |
| Series of hoods/housings | Han-Eco® B |
| Type of hood/housing | Hoods |
| Description of hood/ housing | With integrated cable gland |

## Version

| | |
|---|---|
| Locking type | Single locking lever |
| Size | 16 B |
| Version | Side entry |
| Cable entry | 1x M40 |

## Technical characteristics

| | |
|---|---|
| Limiting temperature | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP66 |
| Clamping range | 16 ... 28 mm |

## Material properties

| | |
|---|---|
| Material (hood/housing) | Polyamide<br>Fibre-glass reinforced |
| Colour (hood/housing) | RAL 9005 (jet black) |
| Material flammability class acc. to UL 94 | V-0 |

## Specifications and approvals

| | |
|---|---|
| Specifications | IEC 61984<br>EN 45545-2 R22: HL1, HL2, HL3<br>EN 45545-2 R23: HL1, HL2, HL3<br>EN 45545-2 R24: HL1, HL2, HL3 |

## Commercial data

| | |
|---|---|
| Packaging size | 1 |


HARTING Electric GmbH & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Pushing Performance

## Commercial data

| | |
|---|---|
| Net weight | 217 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |


HARTING Electric GmbH & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com