

KM 70/20 C

Low-dust sweeping inside and out: the flexible KM 70/20 C manual sweeper achieves optimum cleaning results thanks to its filter, sweeping roller and side brush.



Order no. 1.517-130.0

- Sweeper roller drive via both wheels
- Push handle adjustable to 3 settings
- Infinitely adjustable sweeper roller and side brush

Technical data		
EAN code		4054278809403
Drive type		Manual
Max. area performance	m²/h	2800
Working width	mm	480
Working width with 1 side brush	mm	700
Tank volume, gross/net	l	45 / 20
Colour		anthracite
Weight (with accessories)	kg	21
Package weight	kg	26.4

Equipment	
Fine dust filter	■
Sweeper drive, manual	■
Adjustable main sweeper roller	■
Foldable push handle	■
Dustpan principle	■
Outdoor use	■
Indoor use	■

■ Included in the scope of supply.



Infinitely adjustable sweeper roller and side brush

- Incrementally adjustable contact pressure for optimum sweeping results.
- Adjusting the contact pressure reduces sweeper roller wear.
- To protect the bristles, the sweeper roller and side brush can be completely relieved of load.



Dust filter

- The dust filter cleans the exhaust air and prevents dust from flying up during sweeping.
- The filter system is easily accessible for quick and easy replacement.




Home Base system

- Convenient storage of additional equipment such as buckets and litter pickers.
- Accessories can be kept handy in a pocket on the push handle.

ACCESSORIES FOR KM 70/20 C

1.517-130.0



		Order no.	Description	
FILTERS				
Foam filter				
Set filter	1	2.644-435.0	Plastic filter, water-resistant, washable, reduces maintenance costs.	■
MAIN SWEEPER ROLLER				
Standard roller brush				
Reversing rolling mill standard KM70/20	2	6.907-783.0	Tough standard roller brush with moisture-proof universal bristles for normal soiling on all surfaces. Extremely durable.	■
Main sweeper roller, hard				
Main sweeper roller, hard	3	6.903-999.0	For the removal of stubborn dirt outdoors	□
Main sweeper roller, antistatic				
Main sweeper roller, antistatic	4	6.907-023.0	For sweeping surfaces subject to static build up (e.g. carpets, artificial turf)	□
SIDE BRUSHES				
Standard side brushes				
Side broom standard for replacement	5	2.644-447.0	Standard side brush with moisture-proof universal bristles for normal soiling on all surfaces. Extremely durable.	■
MISCELLANEOUS				
Set side strip cpl.	6	2.644-436.0		■
Skirting sweep tank	7	5.030-124.0		■
Rear skirting	8	5.032-334.0		■
OTHER ACCESSORIES SCRUBBER DRIERS				
Home Base accessories				
Homebase accessory bag	9	5.032-196.0	Additional cleaning equipment can be quite easily and conveniently stowed in the accessory bag on the push handle.	□
ABS litter picker set	10	2.640-908.0	For picking up refuse.	□
TROLLEYS & BUCKET SYSTEMS				
Cleaning				
15 L grey bucket	11	9.212-250.0	Grey bucket with colour coded handle	□
	12	9.212-251.0		□

■ Included in the scope of supply. □ Available accessories.