# ZB 8,3:UNBEDRUCKT - Zack marker strip

0803444

https://www.phoenixcontact.com/gb/products/0803444

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, Strip, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 8.3 mm, Number of individual labels: 10, text field height: 10.5 mm, text field width: 8.3 mm

## Your advantages

- The ZB zack marker strip system is a marking solution for modular terminal blocks and electronics modules with tall marker grooves

## Commercial data

| | |
|---|---|
| Item number | 0803444 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BG2112 |
| Product key | BG2112 |
| Catalog page | Page 46 (C-1-2019) |
| GTIN | 4055626071497 |
| Weight per piece (including packing) | 1.791 g |
| Weight per piece (excluding packing) | 1.791 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

## Technical data

### Product properties

| | |
|---|---|
| Product type | Terminal marking |
| Pitch | 8.3 mm |
| Type | high |

Marking

| | |
|---|---|
| Number of individual labels | 10 |

### Dimensions

| | |
|---|---|
| Width | 8.3 mm |
| Pitch | 8.3 mm |

Text field

| | |
|---|---|
| Text field width | 8.3 mm |
| Text field height | 10.5 mm |

### Material specifications

| | |
|---|---|
| Color | white (RAL 9010) |
| Material | PA |
| Flammability rating according to UL 94 | V2 |
| Components | free from silicone and halogen |

### Environmental and real-life conditions

UV resistance

| | |
|---|---|
| Specification | ISO 4892-2:2013-03 (following) |

Wipe resistance of inscriptions

| | |
|---|---|
| Specification | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 100 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % |

### Standards and regulations

| | |
|---|---|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |

### Mounting

| | |
|---|---|
| Mounting type | latching |

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27281101 |

### ETIM

| | |
|---|---|
| ETIM 9.0 | EC000761 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39131500 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |


Phoenix Contact 2025 © - all rights reserved
https://www.phoenixcontact.com



PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk