

KEWTECH

Professional Test Equipment

The 'Easiest to use' 17th Edition Tester

Fast and easy, the KT64 is a market leading instrument. It comes complete ready to use and has the following features:

- ▲ Non-RCD trip loop impedance circuits
- ▲ RCD auto-test – fast RCD testing
- ▲ Insulation Test at 250V, 500V or 1000V with high voltage warning
- ▲ Continuity with auto-null value maintained even when switched off
- ▲ Test button in test probe



Pat Testing Just Got Easier

Suitable for the occasional and heavy user alike. The KT71 is a manual tester with automatic test sequences. Just select your type of appliance then press start, the KT71 will automatically run through the test sequence and displays the results as well as providing red / green lights for pass / fail at each test.

- ▲ Tests according to the UK code of practice
- ▲ Tests IT equipment safely
- ▲ Special extension lead test facility
- ▲ 500V & 250V insulation test (new standard)
- ▲ Run / earth leakage at mains voltage



17th Edition Single Function Instruments - The Traditionalist's Choice - Proven by The Test of Time



KT35

Insulation / Continuity.

With auto-null and lockdown test button for hands free testing. Three insulation voltages



KT45

Loop Impedance / PSC

Bypasses all RCDs when loop testing. Hi & Low test currents. Lockdown test button for hands free testing



KT56

RCD Tester

Comprehensive tester with 18 ranges



KT60

Combined Loop & RCD

Tester as KT45 & KT56 above

Essential Testing Accessories



ACC50MTL

Be ahead of your audit inspector. Fast checking of your earth bond with incoming gas / water pipes and R2 checks



KEWCHECK R2

Socket adaptor for fast connection for R1+R2 and R2 testing - saves damage to decor



LIGHTMATES are adaptors for fast and safe connection to lighting circuits for continuity & loop testing

Lightmate BC

Lightmate ES

Lightmate SBC

Lightmate SES

Lightmate GU10

Universal Test Leads



Unfused Test Leads with 4mm connectors and probe / croc clips option. For insulation / continuity testers and DMMs

ACC020



Fused Test Leads with 4mm connectors

Fused prods with probe / croc clip option. Extra prods for fast change over from probe to croc clip. For Loop & RCD testers

ACC064



Fused Test Leads with IEC connector

Fused prods with probe / croc clip option. Piggy back facility on earth lead for two wire testing. For Loop / RCD testers

ACC016E

Voltage testers: [KEW1700](#) | [KEW1710](#) | [kewstick](#)
Wiring Testers: [kewcheck 103](#) | [kewcheck 105](#) |
[kewcheck R2](#)
Phase Rotation: [KEW8031F](#)
Proving Unit: [kewprove 2](#)
Light Meter: [KEW5202](#)
Testing Adaptor: [Lightmate](#)



Lightmate TESTING ADAPTOR

Lightmates are an essential testing accessory to facilitate fast and safe testing for Loop Impedance, and R1 & R2 Testing of Lighting Circuits.



