

**CUSTOMER DATA SHEET**

CDS No: **07133010**  
 Product: **WYPALL® L10 WIPERS – Centrefeed rolls/White**

Status: **AUTHORISED**  
 Date: **05/01/04**  
 Replaces: **27.08.03**

Countries sold into: **All European Countries**

**BASESHEET**

Property	Typical Values	Property	Typical Values
Recycled Fibre %	100%	Bleaching Method	ECF
Virgin Fibre %	0%	Ash Content	<2%
Broke – internal waste %	Up to 20%	Textured	Yes

**FINISHED PRODUCT**

Property	Typical Values
Format	Folded/Roll Rolled
Basis Weight/No Plies	g/m <sup>2</sup> /No Plies 25/1
Thickness	mm/sheet N/M
Water Absorbency Capacity	% 500
Water Absorbency Rate	sec 10
Oil Absorbency Capacity	% 425
Oil Absorbency Rate	sec 180
Machine Direction Tensile	N/m/ 1ply 256
Cross Direction Tensile	N/m/ 1ply 228
Wet Cross Direction Tensile	N/m/ 1ply 56
Brightness	% 75
Sheet Count	sheets 600
Sheet Length	mm 380
Sheet Width	mm 206
Roll Diameter	mm 200

**PALLETISATION**

Unit of Sale: 6 items per case	Nett Weight/Case :	7.3Kg		
Case Size L x W x H: 60.0 x 40.0 x 20.6 cm	Max Weight/Case:	8.0Kg		
Type of Packaging: Shrink Wrap & 2 Labels	Dispenser Codes:	7087/7088		
Pallet Type	Euro	0.5 Euro	GKN	0.5 GKN
No. Case/Roll per Pallet	32	24	45	30
No. Cases per Layer	4	4	5	5
No. Layers per Pallet	8	6	9	6

**ADDITIONAL INFORMATION**

**Food Contact Tissue (Kitchen Towel, Napkins & Wipers)**

Germany, Switzerland	BfR Recommendation XXXVI	Yes	<del>No</del>
EU	Council of Europe Guidelines	N/A	N/A
ISO 9001 : 2000		Yes	<del>No</del>

**NOTE**

This data was generated from samples which were taken to be typical of standard product. The data is given for information only. Additional information can be supplied on request.

**CONFIDENTIALITY STATEMENT**

These specifications and the confidential information contained herein are the property of Kimberly-Clark. Copies of this material are the property of Kimberly-Clark and should be made only if absolutely necessary. Copies, like the originals, are considered as trade secrets.