

M18 FUEL 30m x 6mm Non-Conductive Powered Fish Tape Replacement Cartridge

FPFT18ACCY01

- Proprietary Replacement Cartridge Design for Smoother Feeding & Retracting

MODEL VARIANT



INCLUDES

- FPFT18ACCY01 (1)

Categories: Plumbing

PRODUCT SPECIFICATIONS

No load speed (m/min)	0 - 37
Length (m)	30
Width (mm)	6
Weight without battery pack (kg)	3.1
Weight with battery pack if applicable (kg)	with 2.0Ah: 6.43 ; With 12.0Ah: 7.49
Recommended Ambient Operating Temperature	'-18°C to +50°C