

Features

- Jaws move in parallel throughout use.
- Smooth jaws to prevent damage to workpiece.
- Wire can be threaded down throat of plier.
- Long-lasting return spring.
- Jaws case hardened to HRC 57 for durability.
- Zinc-plated handles with detailing for added grip.

RS PRO Smooth Jaws Flat Nose Parallel Plier Return Spring 200 mm

RS Stock No.: 0517565



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Smooth Jaws Flat Nose Parallel Plier

Engineered with smooth parallel jaws for a firm grip without damaging delicate pieces. Return spring for easy handling of parts.

Perfect for working with jewellery and manipulating or straightening soft wire.

Benefits

- Ideal for holding, gripping and manipulating without damage.
- Parallel jaws grip securely along their whole length.
- Hold soft materials in a firm grip without marking.
- Manipulate, straighten and remove kinks in wire.
- Easier handling of parts due to return spring.
- Built to last, with a robust construction and rust-resistant finish.

Applications

A workbench essential, for use with soft metals and other delicate materials. Ideal for:

- Jewellery makers.
- Manufacturers of delicate pieces.
- Hobbyists and craft workers.

General Specifications

Plier Type	Smooth Jaw Flat Nose Parallel Plier
Number of Pieces	1
Overall Length	200 mm
Cutting Capacity	N/A
Material	Steel jaws and zinc-plated steel handles.
ESD Safe	No
Jaw Length	40 mm useable jaw length
Jaw Opening	17 mm
Jaw Width	12.5 mm
Non Sparking	No
Height Safe	No

Approvals

Declarations	REACH DoC
--------------	-----------

Similar Products

Stock No.	Brand	Product Name	Jaw	Parallel	Overall Length	Application
0517562	RS PRO	PARALLEL PLIER	SMOOTH JAW	Yes	125 MM	Working with small components and in tight spaces
4960-160	RS PRO	SIDE CUTTER PARALLEL PLIER	SERRATED JAW WITH CUTTER	Yes	160 MM	Multi-purpose tool, for gripping, manipulating and cutting
4960-140	RS PRO	SIDE CUTTER PARALLEL PLIER	SERRATED JAW WITH CUTTER	Yes	140 MM	Multi-purpose tool, for gripping, manipulating and cutting
4951-140	RS PRO	SIDE CUTTER PARALLEL PLIER	SERRATED JAW WITH CUTTER	Yes	140 MM	Multi-purpose tool, for gripping, manipulating and cutting
4950-125	RS PRO	SIDE CUTTER PARALLEL PLIER	SERRATED JAW WITH CUTTER	Yes	125 MM	Multi-purpose tool, for gripping, manipulating and cutting
549-331	RS PRO	SIDE CUTTER PARALLEL PLIER	SERRATED JAW WITH CUTTER	Yes	160 MM	Multi-purpose tool, for gripping, manipulating and cutting

