PRODUCT-DETAILS

L-10-50R-0-C

CABLE TIE 50LB 12IN UV BLK NYL RLSB

General Information

Extended Product Type	L-10-50R-0-C
Product ID	7TAG054750R0009
EAN	5414363077992
Catalog Description	CABLE TIE 50LB 12IN UV BLK NYL RLSB
Long Description	Releasable Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Length of 302mm (11.89 Inches), Width of 7.6mm (0.3 Inch), Thickness of 1.5mm (0.06 Inch), Tensile Strength Rating of 222 Newtons (50 Pounds)

Ordering

EAN	5414363077992
UPC	728494910000

Dimensions

Product Net Width	0.3 in 7.6 mm
Product Net Depth / Length	11.89 in 302 mm

Container Information

Package Level 1 Units	100 piece

Package Level 1 Width	5.8 in 147 mm
Package Level 1 Height	1.95 in 50 mm
Package Level 1 Depth / Length	13.65 in 347 mm
Package Level 2 Units	5000 piece
Package Level 2 Width	13.4 in 340 mm
Package Level 2 Height	13.2 in 335 mm
Package Level 2 Depth / Length	17.5 in 445 mm

Technical UL/CSA

Flammability According to UL94	V-2

Additional Information

Brand / Label	Catamount
Bundle Diameter	0.28 to 3.15 in 7 to 80 mm
Color	Black
Effective Date	19960215
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6 Weather Resistant
Number of Batteries	0
Product Name	NYLON CABLE TIES
Product Type	Releasable
Standards	UL E49405
Tensile Strength	50 lb 222 N
Thickness	0.06 in 1.5 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	L-10-50R-0-C
Instructions and Manuals	L-10-50R-0-C

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties