2531: Mother Jaw 32 kN for Inserts for model P25+

The + product :

Weight and space gain thanks to the insert concept.
Compatible: Use with Virax inserts.
Versatile: Adaptable to most electrohydraulic machines in the market.

Description

Economical:
The system [mother jaw + inserts] pays for itself promptly. On average, a set of inserts is twice cheaper than standard crimping jaws.

Practical:
Light and compact in the toolbox instead of standard crimping jaws.
On average, an installation requires 5 sets of inserts (different profiles or diameters). The weight of the mother jaw and 5 sets of inserts is only 2.6 kg, instead of over 10 kg for 5 standard crimping jaws.

Compatible:
Use with Virax inserts on your Virax Viper® P25+ press-fitting machine.
Ball locking is a good compromise between holding and easy extraction of inserts.

Versatile:
The Virax 32 kN mother jaw is assembled on market-standard 32-34 kN power electrohydraulic machines, such as the Virax VIPER® P25+.

Dimensions (mother jaw only): 151 x 103 x 39 mm.
Weight (mother jaw only): 1.480 kg.
Not compatible with electromechanical machines, such as the Virax Viper® P30+.

Find compatibility with VIRAX fitting systems and inserts/clips using the Vir-app application or at the end of the catalogue.

More Information

Capacity	Copper: Ø 12 – 28 mm / Ø 1/4 - 7/8". Stainless steel: Ø 12 – 28 mm. PER, PEX: Ø 12 – 32 mm. Multilayer: Ø 12 – 32 mm. Electro-zinc steel (or carbon steel): Ø 12 – 28 mm.
Supplied with	The mother jaw itself, ref. 253163, and the mother jaw + insert kits are delivered in Virabox case, with 10 slots for insert sets.

References

Sku	Description	Size mm	Crimping force kN	kg
253170	Mother Jaw 32 kN + Inserts RF-P12/RF-P16/RF-P20/RF-P/25	390 x 190 x 120	32	3,120
253163	Mother Jaw 32 kN alone	390 x 190 x 120	32	2,390
253164	Mother Jaw 32 kN + Inserts TH16/TH20/TH26	390 x 190 x 120	32	3,100
253165	Mother Jaw 32 kN + Inserts V12/V14/V16/V18/V22	390 x 190 x 120	32	3,190
253166	Mother Jaw 32 kN + Inserts M12/M15/M18/M22/M28	390 x 190 x 120	32	3,325
253167	Mother Jaw 32 kN + Inserts U16/U20/U25	390 x 190 x 120	32	2,860
253168	Mother Jaw 32 kN + Inserts HA16/HA20/HA26	390 x 190 x 120	32	3,450
253169	Mother Jaw 32 kN + Inserts RF-P12/RF-P16/RF-P20	390 x 190 x 120	32	2,970