HIRSCHMANN® Test & Measurement
A BRAND OF SKS

SKS Kontakttechnik GmbH

Sockets

BIL 30

CE

Product	BIL 30
description	Socket with insulated head and ring for installation in equipment chassis and switchpanels up to 4 mm wall thickness. 4 mm diameter gold-plated zinc die-cast socket, with solder connection.
operating instruction	BA403
article-no. / *colour	9301661xx 00 black · 01 red · 02 blue · 03 yellow · 04 green · 05 brown · 06 gray · 07 white · 09 violet Sn
drawing	
	
technical data	
connection	M6 thread, solder connection
rated voltage(1)	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O (3)
rated current(1) (consider derating curve)	32 A
housing material	PA
temperature range acc. To IEC61010(2)	-25 °C to +85 °C
inflammability class acc. to UL 94 (only valid for basic material of housing)	V-2

4 mm system

(1) for normal environmental conditions 5°C to 40°C
(2) contact the manufacturer for applications at deviating temperature ranges
(3) without rated measurement category, for other circuits that are not directly connected to mains
stand: 17.08.2022