



DEWALT 18V XR Brushless Hammer Drill - 1x 5Ah

DCD709P1T-GB



- 175mm in length, allowing you to get into even smaller spaces
- 1.2kg (tool only) for ultimate portability and ease of use
- Efficient Brushless motor delivers high performance, extends tool life and allows for a much shorter design
- Foot LED with delay feature for better workpiece illumination
- 15 position adjustable torque control for consistent screw driving into a variety of materials
- 65Nm torque allows you to achieve tough applications
- Includes 1 x 5Ah battery, multi-voltage charger and TSTAK kitbox

Description:

The DEWALT 18V XR Brushless Hammer Drill has been constructed to be heavy duty yet lightweight and compact. The Brushless motors run cooler and more efficiently, enabling more power to be delivered during application, resulting in less wear. The powerful hammer drill is compact with a length of 175mm. The 2 speed Brushless motor delivers 65Nm of torque and extended runtime, this drill is capable of even the most demanding applications. Other features include a foot LED for better workpiece illumination and a belt hook for easy carrying when not in use.

Supplied With:

- 1 x 18V XR 5Ah Batteries
- 1 x Battery Charger
- 1 x T-STAK Kitbox

Typical Applications:

Cordless drills are appropriate for wide range applications such as drilling holes, driving nuts and bolts etc. They are ideal for household and heavy construction jobs and typically used by:

- Construction works
- Demolition works
- Plumbing systems installation
- Electrical systems installation
- Carpentry industry

FAQs:

What do I get in the set?

The DeWalt DCD709P1T comes with:

- *1 x 18 Volt 5.0Ah Li-Ion Batteries*
- *Multi-Voltage XR Charger*
- *Magnetic Bit Holder*
- *T-Stak Carry Case*

Do you stock compatible batteries for this drill?

The drill is compatible with all 18V XR series batteries as well as FlexVolt 18V/54V batteries. Full range of compatible batteries you can be find in Power Tool Batteries

What motor does the drill have?

The drill features a brushless motor for increased efficiency and power delivery for longer tool life.

Do the batteries of this tool fit other Dewalt products?

This product comes with a 5.0Ah 18V XR Li-ion Battery, which is interchangeable across the whole DEWALT 18V range.

Specifications	
Battery	XR Lithium-Ion
Voltage	18 V
Max Torque (Hard)	65 Nm
Chuck Capacity	1.5-13 mm
No of Speeds	2
No Load Speed (Drilling/ Driving/ Hammer Mode)	0-450/0-1650 rpm
Beats Per Minute	0-7650/0-28050 bpm
Max Drilling Capacity [Wood]	30 mm
Max Drilling Capacity [Metal]	13 mm
Max Drilling Capacity [Masonry]	13 mm
Length	175 mm