HellermannTyton

Technical data sheet

Article number:
924-00505 BLU1.5

Product Group	Un-Insulated Bootlace Ferrules
Product Family	Bootlace Terminals
Material	Copper (CU)
Colour	Silver-matt (MTSR)

Application Range	Low Voltage
Conductor Size (mm^2)	1.5 mm^2
Diameter (D)	2.8 mm
Length (L)	8 mm
Length (L2)	7 mm
Max Voltage	600 V
Operating Temperature	-55 °C to +155 °C
Package Content packed in	bag
REACh Reg. Art.33 does not contain SVHC	Yes
Ø (D2)	1.7 mm
ROHS compliant	Yes

RoHS

created on 11. May 2026, 12:34 pm

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.