Rittal – The System.

Faster – better – everywhere.

Toroidal transformer Primary connection 115 V/400 V – SK 3201.970

Date : Apr 26, 2021

ENCLOSURES POWER DISTRIBUTION CLIMATE CONTROL IT INFRASTRUCTURE SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

Toroidal transformer Primary connection 115 V/400 V – SK 3201.970

created: 26.04.2021 build on www.rittal.com/uk-en



Product description

Description:	For the power supply of wall-mounted 230 V air/water heat exchangers. Available with 115 V or 400 V primary connection.
Technical specifications:	Output 110 VA Voltage tolerance ±10% Primary connection 3500 mm long Secondary connection 1500 mm long For mounting on a 35 mm support rail EN 50 022
Supply includes:	Toroidal transformer Assembly parts
To fit Model No.:	3363.X0X 3364.X0X 3214.100 3214.700 3215.100 3215.700

Product description

Rated operating voltage:	115 V (primary) , 1~, 50 Hz/60 Hz 230 V (secondary) , 1~, 50 Hz/60 Hz
Dimensions:	Width: 105 mm Height: 123 mm Depth: 55 mm
Snaps onto a support rail TS 35:	yes

eCl@ss 8.0/8.1:	27180704
Packs of:	1 pc(s).
Weight/pack:	2.23 kg
EAN:	4028177690233
Customs tariff number:	85043121
ETIM 7.0:	EC000855
ETIM 6.0:	EC000855
eCl@ss 8.0/8.1:	27180704
eCl@ss 6.0/6.1:	27189269
Product description:	SK Toroidal transformer, 115 V (primary), 1~, 50/60 Hz, 230 V (secondary), 1~, 50/60 Hz, WHD: 105 x 123 x 55 mm

Approvals

Certificates:	EAC
Declarations:	Declaration of conformity