


# INB IO 80-6 BU - Insertion bridge



3246931

<https://www.phoenixcontact.com/gb/products/3246931>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Insertion bridge, Bridging in the terminal point, latching in the terminal housing, number of positions: 80, color: blue

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3246931       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | BE1Z2X        |
| Product key                          | BEKZ2X        |
| GTIN                                 | 4046356706193 |
| Weight per piece (including packing) | 34.7 g        |
| Weight per piece (excluding packing) | 34.59 g       |
| Customs tariff number                | 85389099      |
| Country of origin                    | DE            |

# INB IO 80-6 BU - Insertion bridge

3246931

<https://www.phoenixcontact.com/gb/products/3246931>



## Technical data

### Product properties

|                     |                  |
|---------------------|------------------|
| Product type        | Insertion bridge |
| Number of positions | 80               |
| Potentials          | 80               |

### Material specifications

|                     |                 |
|---------------------|-----------------|
| Color               | blue (RAL 5015) |
| Material            | Cu              |
| Insulating material | PA              |

# INB IO 80-6 BU - Insertion bridge



3246931

<https://www.phoenixcontact.com/gb/products/3246931>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250303 |
| ECLASS-15.0 | 27250303 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000489 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# INB IO 80-6 BU - Insertion bridge



3246931

<https://www.phoenixcontact.com/gb/products/3246931>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)