KERN **ODC 852**

Specialists in microscopy for measurement, counting, documentation, archiving and image processing

Category

Brand	Optics
Product category	Microscope
Product group	Microscope camera
Product family	ODC-85

Construction

Dimension (W×D×H)	92×68×68 mm
HDMI cable length	2000 mm

Functions

Camera - Applicable software	Microscope VIS 2.0 Pro (OXM 902) integrated camera software (HDMI)
Supported operating systems	Win 8 Win 10 Win 11
Memory - total size	16 GB
System requirements CPU	Quad-Core, x64
System requirements RAM	8 GB
System requirements SSD storage	256 GB SSD
System requirements graphics card	DirectX 12
System requirements screen	20" HD or larger
System requirements clock speeds	2.8 GHz

Interface

Interfaces	WiFi USB 2.0 HDMI SD card slot

Focussing

Auto-focus	✓

Camera

Cameratype	HDMI Microscope Camera (AF) - C-Mount
Camera - Resolution	5 MP
Camera - Sensor type	Sony CMOS
Camera - Sensor size	1/1,8"
Camera - Colour depth	Colour
Camera- Mounting types	C-mount
Camera - Exposure method	Rolling Shutter
Camera - Sensor dimensions	6,22×4,67 mm
Camera - Pixel size	2,4×2,4 µm
Camera - FPS range 1	30 FPS
Camera - Resolution range 1	1920x1080
Camera - FPS range 2	25 FPS
Camera - Resolution range 2	1920x1080
Camera - Exposure time [Min]	0,03 ms
Camera - Exposure time [Max]	918 ms

Power Supply

Supplied power supply	Power supply unit
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	AUS UK US CH
Input voltage power supply / power [Max]	100 V - 240 V AC 50/60 Hz 0,3 A
Power supply cable removable	removable
Input voltage device / power [Max]	12 V, 1.0 A
Power socket for mains adapter	Inside plus, outside minus

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓

Packing & Shipping

Delivery time	1 d

KERN **ODC 852**

Specialists in microscopy for measurement, counting, documentation, archiving and image processing

Dimensions packaging (W×D×H)	225×170×90 mm
Shipping method	Parcel service
Net weight approx.	1,00 kg
Gross weight approx.	1,8 kg
Shipping weight	1,6425 kg
Shipping volume weight	0,7 kg

Product information

GTIN/EAN number	4045761235731
Trade number	90119000
REACH classification	no prohibited substances

Pictograms

STANDARD

OPTION