RS Pro 7000 Lumen LED Tripod Floodlight

RS Stock No.: 0757763

Features

- Foldable tripod LED light
- Uses white LEDs,
- Using 2*21700 7.4 V 4000mAh battery,
- Function: low – medium – high – OFF
- Brightness: 1500lms--4000lms--7000lms
- Runtime: 7hrs-3.5hrs-1.5hrs
- Charging time: 5hrs (5V 2A)
- Dimensions: 800*100*95mm(folded), head size: 210*100*95mm, the height can reach 1.7meter after expanded
- With power bank function



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS Pro 7000 Lumen LED Tripod Floodlight is a compact, high- output triple-head rechargeable floodlight designed for general worksite lighting, mobile task use, and low- profile area coverage. Delivering up to 7000 lumens from three COB LEDs totaling an output of 70 W, the light provides enhanced versatility in both close- up and mid- range applications.

The unit features a large folding tripod ensures that the light can be set up in whatever position suits your needs. Built for durability, the housing is IP54-rated for water and dust protection and certified IK07 for impact resistance. Output options include 1500 / 4000 / 7000 lumens in flood mode (1.5 to 7 hours of runtime). Onboard LEDs provide charge and discharge status at a glance.

General Specifications

Floodlight Type	Tripod light
Luminosity	7000lms
Switch Mode / Lumens / Runtime	low- medium- high-OFF , 1500lms--4000lms--7000lms , 7hrs-3.5hrs-1.5hrs
Lumen Efficiency	100lm/W
Light Colour	white
Colour Temperature	6500k
Colour Index (CRI)	80
Beam Angle	120°
Case Material	aluminium
Housing Colour	Black, blue
Applications	Auto repair, outdoor, indoor, garage, warehouses, construction areas

Electrical Specifications

Wattage	70w
DC Charge Voltage	5v
DC Charge Current Rating	2A
Incandescent Equivalent Wattage	460 W
Frequency Range	TYPE C 5V DC POWER SUPPLY
Power Factor (PF)	1
Plug Type	TYPE-C
Fixture Connection	USB Cable
Lamp Type	LED
Solar Panel	NO
Dimmable	NO
Life Hours	100000hours
Lamp Supplied	yes
Lamp's Efficiency (%)	>90

Mechanical Specifications

Dimensions	800*100*95mm(folded),
Height	1.7meter when open the tripod
Width	100mm
Depth	800mm
Reflector Shape	Symmetric
Mounting Method	Surface

Operation Environment Specifications

Operating Temperature Range	-10℃~+50℃
Minimum Operating Temperature	-10℃
Maximum Operating Temperature	+50℃

Protection Category

IP Rating	IP54
IK Rating	IK07

Approvals

Compliance / Certifications	CE /ROHS


图纸比例1：4


RS PRO


RS PRO





