1915D Braided polyurethane hose, 95 Shore, 9 metres long

- Flexible, lightweight, hard-wearing hoses, designed for maintenance jobs in small and open areas
- Resistant to low temperature (-40 °C)
- Female/female threaded connectors

	art.		D1xD mm	Ø GAS BSP
019150017	1915D 8X12	1915D 8X12-braided polyurethane hose	8x12	1/4"



