
Features

- Stainless steel confined space entry barrier
- 1.2 mm thick SS sheet construction
- Scissor-style expandable arm mechanism
- Fixed installation with nuts and bolts
- Includes 4 nuts & 4 bolts
- Integrated hazard warning sign
- Corrosion-resistant and long-lasting
- Designed for confined space safety control

RS PRO Sign-o-Barrier Stainless Steel for up to 40-inch Confined Space Opening

RS Stock No.: 0802247



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- ***Heavy-Duty Stainless Steel Construction*** *- Manufactured from 1.2 mm stainless steel sheet, offering superior strength, durability, and corrosion resistance.*
- ***Physical Access Restriction*** *- Acts as a solid mechanical barrier to prevent unauthorised personnel from entering confined spaces.*
- ***Integrated Warning Signage*** *- Includes a clear hazard warning sign to alert employees and bystanders not to enter without authorisation.*
- ***Scissor-Arm Expansion Mechanism*** *- Four-arm scissor-like structure enables: Easy installation, Adjustable positioning, and Compact storage after use*
- ***Secure Mounting System*** *- Can be firmly attached using nuts and bolts at the confined space opening.*
- ***Complete Installation Hardware Included*** *- Supplied with 4 nuts and 4 bolts for immediate deployment.*

General Specifications

Type	Confined Space Lockout Cover
Material	Stainless steel
Colour	Metallic Silver
Package	LD + Carton Box

Mechanical Specifications

Size	1016mm (40 Inches)
Inner Circle	1.5 Feet
Thickness	1.2mm
Weight	3.4 Kgs

Operation Environment Specifications

Withstand temperature	-40°C to 120°C






DANGER