KERN **FPB 15K-3**

Robust bench scale with IP68/IP69K protection and checkweighing display

Category

Brand	KERN
Product category	Industrial scale
Product group	Bench scale
Product family	FPB

Measuring System

Weighing system	Strain gauge
Number of weighing ranges	1
Weighing capacity [Max]	15 kg
Readability [d]	0,001 kg
Reproducibility	0,001 kg
Linearity	± 0,003 kg
Resolution	15.000
Tare range	15 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	15 kg (M1)
Possible calibration points	15 kg
Stabilization time	2 s
Eccentric loading at 1/3 [Max]	0,005 kg
Construction type of the scale	Single-range balance
Units	kg g lb oz PCS tJ lb:oz
Units (if device is conformity assessed)	kg g
Load cell connection	4-wire
Maximum creep (15 minutes)	4 g
Maximum creep (30 minutes)	8 g
Default unit	kg
Loadcell type	Tscale BX6

Display

Display type	LCD
Display backlight	✓
Display screen size	100×35 mm
Display segments	7
Display digit height	25 mm
Languages of the user interface	English

Construction

Dimension housing (W×D×H)	288×233×102 mm
Dimensions completely mounted (W×D×H)	288×233×102 mm
Dimensions weighing surface (W×D)	190×230 mm
Dimensions weighing surface	190×230 mm
Dimensions weighing platform (W×D×H)	230×190×20 mm
Material housing	stainless steel, plastic
Material weighing plate	stainless steel
Material load cell(s)	aluminium
Level indicator	✓
Levelling feet adjustable	✓

Functions

Tolerance weighing	✓
Tolerance weighing - type of signal	visual
Counting function	✓
Counting resolution (laboratory conditions)	15.000
Smallest piece weight when piece counting - laboratory conditions	1 g
Smallest piece weight when piece counting - normal conditions	10 g
Reference quantity	10, 20, 50, 100, 200
IP protection - complete device	IP68 IP69K
Auto-off interval(s) in battery mode/rechargeable battery mode	selectable
Auto-off interval(s) in mains power mode	selectable
Tare function	manual (multi)
Number of keys for operation	4

KERN **FPB 15K-3**

Robust bench scale with IP68/IP69K protection and checkweighing display

Power Supply

Supplied power supply	Accu & Power supply
Power supply type	USB including power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	EURO
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Power supply cable removable	removable
Input voltage device / power [Max]	5 V, 1 A
Power socket for mains adapter	Hollow plug inside plus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 9,4 mm
Battery / accumulator type	Li-Ion
Battery capacity	4.000 mAh
Battery voltage	3,7 V
Battery – Number of cells	2
Battery – Individual weight	154 g
Battery – Total weight	308 g
Battery – Construction	Inseparable connection of cells (pack)
Battery capacity (Wh)	14,8 Wh
Battery – Tests passed UN 38.3	✓
Rechargeable battery operating time - backlight on	400 h
Rechargeable battery operating time - backlight off	500 h
Rechargeable battery charging time	4 h
Battery/Accu connected	not connected, enclosed

Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Humity of environment [Min]	5 %
Humity of environment [Max]	85 %
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓

Services (optional)

Article number for adjustment at the location of installation	961-248
Article number for DAkkS calibration	963-128
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	340×295×165 mm
Shipping method	Parcel service
Net weight approx.	2,2 kg
Gross weight approx.	3,4 kg
Shipping weight	3,3 kg
Shipping volume weight	3,3 kg

Product information

GTIN/EAN number	4045761488496
Trade number	84238129
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION