Universal Minimess® Pressure Test Kit

Features

- All major test point variants covered with one kit. The ultimate service tool.
- Connect & disconnect under full system pressure. Lifetime leak free guarantee.
- In-line test point tees offer excellent system access versatility.
- Amazing value for range of testing capabilities included.

RS PRO Universal Minimess® Pressure Test Kit

RS Stock No.: 0848937




RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.


Universal Minimess® Pressure Test Kit

Technical Specifications

- 2 x 63mm glycerine filled pressure gauges user selectable up to 700 bar.
- 3 x Minimess® Male/Swivel Female 1620 inline test point adaptors. 1/4", 3/8" & 1/2" BSP.
- 4 x Minimess® 1620 changeover adaptors from 1215, 1615, HSP (5/8"BSF) & F/F Quick Release
- 1 x Minimess® 1620 test point - 1/4" BSP male threaded.
- 1 x G1/4" BSP to 1620 gauge adaptor.
- 2 x 630 bar rated Minimess® pressure test hoses (1620 & Steck) - 1.5 meters long.
- Additional 3/8" & 1/2" BSP male threaded adaptors & seals.







Ordering Codes

0848937	RS PRO Universal Minimess Pressure Test Kit. 2x 63mm 0..40 and 0..400 bar glycerine gauges, multi-format test point adaptors, 2 hoses.