Lighting **excellence**

@4liteuk @4liteuk

@4lite @4liteuk

# Valde

| | |
|---|---|
| **Application** | Industrial |

Valde IP65 Non Corrosive Multi Wattage 1500mm Microwave Sensor
Code: 4L3/1141/MW





## Product Features

- 3 CCT colour selectable feature
- Hybrid body size
- Multiple cable entry / conduit entry points
- Adjustable sliding fixing bracket
- Multi wattage
- Available in 1200mm / 1500mm / 1800mm lengths
- Detachable terminal block with multiple positions adjacent to all cable entry points
- Also available as Emergency and Microwave options

| Technical Information | |
|---|---|
| **Wattage** | 33W / 45W / 51W / 60W |
| **Lumens Delivered** | 4620lm - 8400lm (4000K) |
| **Lm/W** | 140lm/W |
| **Beam Angle** | 120 |
| **CRI** | 80 |
| **CCT** | 3000K/4000K/6500K |
| **Input** | 220-240V |
| **Operating Temp** | -20°C - 40°C |
| **SDCM** | 6 |
| **UGR** | 25 |

| Technical Information | |
|---|---|
| **Light Source** | LED |
| **Colour / Finish** | Grey |
| **IP Rating** | IP65 |
| **Class Protection** | 1 |
| **Internal / External** | Internal / External |
| **Mounting Option** | Surface, Suspended |
| **Lumen Depreciation** | L70 50,000h |
| **Warranty (Years)** | 4 |
| **CE Mark** | Yes |
| **Height** | 75 mm |