06950020

RCK 95 - Rigid joint

2D Technical Drawing



Dynamic 3D View

Technical Specifications

Part number (CODE)	06950020
Ød (DD) mm	20
ØD (D) mm	50
L1 (L1) mm	50
L (L) mm	56
Maximum torque Mt (MT) Nm	240
Clamping pressure - Shaft (CPS) N/mm^2	105
Clamping screws DIN 912 MAT. 12.9 - Num. (CSN)	4
Clamping screws DIN 912 MAT. 12.9 - Type (CST)	M6x40
Clamping screws DIN 912 MAT. 12.9 - Torque (CSTQ) Nm	17
Weight (WEIGHT) kg	0.50