KERN **YKG-01**

Dot matrix printer

Category

Brand	KERN
Product category	Balance
Product group	Printer

Construction

Dimension (W×D×H)	160×245×140 mm
Material	plastic

Interface

Interfaces	RS-232 standard

Power Supply

Supplied power supply	Power supply unit
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	UK
Input voltage power supply / power [Max]	100 V - 240 V AC, 50 / 60 Hz
Power supply cable removable	removable
Input voltage device / power [Max]	24 V DC 1,5 A
Power socket for mains adapter	3-pole round plug

Environmental conditions

Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C

Approval

CE mark	✓

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	330×300×220 mm
Shipping method	Parcel service
Net weight approx.	2,8 kg
Gross weight approx.	3,8 kg
Shipping weight	4,4 kg
Shipping volume weight	4,4 kg

Product information

GTIN/EAN number	4045761253056
Trade number	84239010
REACH classification	no prohibited substances

Pictograms

STANDARD