1/2" 12-POINT SOCKETS - METRIC | E117062



Description

- ISO 2725-1 - DIN 3124 - ISO 1174-1 - ISO 1711-1 - ISO 691
- Chrome vanadium steel.
- OGV® profile: tightening torque applied to the sides rather than to the angles of the nut.
- High Chrome finish.
- For manual use.

Information

EAN	3258951170625
A [mm]	19
d1 [mm]	26.3
d2 [mm]	26.3
H [mm]	43
L [mm]	38
L1 [mm]	16.7
Conditioning	1
[g]	84