0430 : HSS Saw Blade





Description

New High speed and precise HSS bi-metal saw blade:
- 18 teeth or 24 teeth per inch : blade perfect for steels, but also aluminium, stainless steel, PCV or wood, high thickness (18 TPI) or medium thickness (24 TPI)
- 32 teeth per inch : blade perfect for copper, but also aluminium and stainless steel, small thickness.

Overheating resistance: high longevity.
Flexible blade to be able to cut in difficult to access locations.

References

Sku	Use	Number of teeth per inch	Number of teeth per cm	Recommended thickness mm	L mm	Packaging	kg
043008	Steel	18	8	6-25	300	100	1,740
043004	Steel	24	10	3-6	300	10	0,174
043010	Steel	24	10	3-6	300	100	1,740
043006	Copper	32	12	1-3	300	10	0,174
043012	Copper	32	12	1-3	300	100	1,740

