


3M Science.
Applied to Life.™

3M™ ScotchCode™ Wire Marking and Identification System



Identify with 3M

Dispensers

3M™ ScotchCode™ Wire Marker Tape Dispenser STD

The 3M™ ScotchCode™ Wire Marker Tape Dispenser STD is a compact, carry-along dispenser with ten refillable compartments which hold eight-foot rolls of non-smear polyester tape. The tape's high tack, acrylic adhesive resists solvents, oil and water and adheres firmly to insulation surfaces. An end loop hooks the dispenser easily to a tool pouch or belt. Dispensers can be ordered empty or filled with 10 rolls of either pre-printed numbers 0-9 or NEMA colors.



Features

- Compact design
- Hangs from a tool belt
- Helps provide contamination protection around the wire markers
- Can be custom filled to meet specific project requirements
- Dispenses only the desired length

Specifications and Ordering Information for 3M™ ScotchCode™ Wire Marker Tape Dispensers

Product Number	UPC (054007-)	Description	Case Qty.
STD	12172	Dispenser only—holds 10 rolls	25
STD-X	49519	Dispenser only—holds 10 rolls	10
STD-0-9	12174	Dispenser filled with 10 rolls of numbered tape (one each of 0–9)	25
STD-0-9X	49518	Dispenser filled with 10 rolls of numbered tape (one each of 0–9)	10
STD-C	12175	Dispenser filled with 10 rolls of colored tape (one each of black, blue, brown, green, gray, orange, red, violet, white and yellow)	25
STD-CX	49517	Dispenser filled with 10 rolls of colored tape (one each of black, blue, brown, green, gray, orange, red, violet, white and yellow)	10

3M™ ScotchCode™ Wire Marker Tape Refill Rolls SDR

3M ScotchCode Wire Marker Tape Refill Roll SDR is available in ten NEMA colors, individual numbers and consecutive numbers, letters and symbols.

The SDR tape can be used for applications with operating temperatures between -40°F (-40°C) to 250°F (121°C):

- Marking all types of wire and cable including power, control, fiber optic, electronic, telecommunications, and instrumentation
- Phase identification on large or small gauge wire or cable
- Identification of terminal blocks, terminal strips, and wire in panel boards or a piece of switchgear
- Automotive applications on tubing, hoses and replacement parts



Specifications and Ordering Information for 3M™ ScotchCode™ Wire Marker Tape Refill Rolls SDR

Product Number	UPC (054007-)	Description	Inner Unit Pack	Case Qty.
SDR-0	09369	0	10/box	50
SDR-1	09370	1	10/box	50
SDR-2	09371	2	10/box	50
SDR-3	09372	3	10/box	50
SDR-4	09373	4	10/box	50
SDR-5	09374	5	10/box	50
SDR-6	09375	6	10/box	50
SDR-7	09376	7	10/box	50
SDR-8	09377	8	10/box	50
SDR-9	09378	9	10/box	50
SDR-0-9	09368	Consecutive 0–9	10 rls/pk	50 rolls or 5 packs
SDR 10-19	09379	Consecutive 10–19	10 rls/pk	50 rolls or 5 packs
SDR 20-29	09380	Consecutive 20–29	10 rls/pk	50 rolls or 5 packs
SDR 30-39	09381	Consecutive 30–39	10 rls/pk	50 rolls or 5 packs
SDR 40-49	09382	Consecutive 40–49	10 rls/pk	50 rolls or 5 packs
SDR 50-59	09383	Consecutive 50–59	10 rls/pk	50 rolls or 5 packs
SDR 60-69	09384	Consecutive 60–69	10 rls/pk	50 rolls or 5 packs
SDR 70-79	09385	Consecutive 70–79	10 rls/pk	50 rolls or 5 packs
SDR 80-89	09386	Consecutive 80–89	10 rls/pk	50 rolls or 5 packs
SDR 90-99	09387	Consecutive 90–99	10 rls/pk	50 rolls or 5 packs
SDR-A	09388	A	10/box	50
SDR-B	09389	B	10/box	50
SDR-C	09390	C	10/box	50
SDR-D	09391	D	10/box	50
SDR-E	09392	E	10/box	50
SDR-F	09393	F	10/box	50
SDR-G	09394	G	10/box	50
SDR-H	09395	H	10/box	50
SDR-I	09396	I	10/box	50
SDR-J	09397	J	10/box	50
SDR-K	09398	K	10/box	50
SDR-L	09399	L	10/box	50
SDR-M	09403	M	10/box	50



Specifications and Ordering Information for 3M™ ScotchCode™ Wire Marker Tape Refill Rolls SDR

Product Number	UPC (054007-)	Description	Inner Unit Pack	Case Qty.
SDR-N	09405	N	10/box	50
SDR-O	09406	O	10/box	50
SDR-P	09407	P	10/box	50
SDR-R	09409	R	10/box	50
SDR-S	09410	S	10/box	50
SDR-T	09411	T	10/box	50
SDR-U	09415	U	10/box	50
SDR-V	09416	V	10/box	50
SDR-W	09417	W	10/box	50
SDR-X	09418	X	10/box	50
SDR-Y	09419	Y	10/box	50
SDR-Z	09420	Z	10/box	50
SDR-L1	09400	L1	10/box	50
SDR-L2	09401	L2	10/box	50
SDR-L3	09402	L3	10/box	50
SDR-T1	09412	T1	10/box	50
SDR-T2	09413	T2	10/box	50
SDR-T3	09414	T3	10/box	50
SDR- + (Plus)	09421	+	10/box	50
SDR- - (Minus)	09422	-	10/box	50
SDR-BK	09423	Black	10/box	50
SDR-BL	09424	Blue	10/box	50
SDR-BN	09425	Brown	10/box	50
SDR-GN	09426	Green	10/box	50
SDR-GY	09427	Gray	10/box	50
SDR-RD	09429	Red	10/box	50
SDR-VL	09458	Violet	10/box	50
SDR-WH	09430	White	10/box	50
SDR-YL	09431	Yellow	10/box	50
SDR-MC	09404	Multiple Colors	10/rls/pk	50 rolls or 5 packs

Books

3M™ ScotchCode™ Pre-Printed Wire Marker Books SPB

When you need to mark wires quickly, try 3M™ ScotchCode™ Pre-Printed Wire Marker Books SPB. These handy books, 15 in all, contain printed vinyl coated cloth wire and terminal markers with clearly printed letters, numbers and industry-standard legends.



Specifications and Ordering Information for 3M™ ScotchCode™ Pre-Printed Wire Marker Book SPB


Product Number	UPC (054007-)	Quantity (each)	Contents	Inner Unit Pack	Case Qty.
SPB-01	49951	45 15	0-9 L1-L3, T1-T3	1/bag	5
SPB-02	49952	10	A-Z, 0-15, +, -, /	1/bag	5
SPB-03	49953	10	1-45	1/bag	5
SPB-04	49954	150	1, 2, 3	1/bag	5
SPB-05	49955	150	A, B, C	1/bag	5
SPB-06	49956	150	T1, T2, T3	1/bag	5
SPB-07	49957	150	L1, L2, L3	1/bag	5
SPB-08	49958	6 4 2	1-15 16-90 A-Z, +, -, /, 0	1/bag	5
SPB-09	49959	45 30	1,2,3,A,B,C L1-L3, T1-T3	1/bag	5
SPB-11	49960	15	1-30	1/bag	5
SPB-12	49961	15 8 6 21	A-Z + — Write-On Markers	1/bag	5
SPB-13	49962	45 33 27 21	+ , - , AC, DC POS, NEG, GND NEUT, SPARE Write-On Markers	1/bag	5
SPB-14	49963	10	46-90	1/bag	5
SPB-15AS	49964	9 5 2 21	30 Alarm System Legends* 1-15 16-45 Write-On Markers	1/bag	5
SPB-16LC	49965	5 110	68 Load Center Legends** Write-On Markers	1/bag	5

* 30 Alarm System Legends: + Circuit +, - Circuit -, + Dc, -Dc, Ac Ac, Zone 1, Zone 2, Zone 3, Zone 4, Zone 5, Zone 6, Zone 7, Zone 8, Zone 9, Shunt, Ground, Fire, Ba Ba, Feed, Return, Phone Feed, Phone Return, Bell, Annunciator, Tamper, 12 Volt, 16 Volt, 24 Volt, Smoke Detector, Thermostat.

**68 Load Center Legends: Main, Refrigerator, Freezer, Range, Disposal, Compactor, Dishwasher, Kitchen Lights, Kitchen Outlets, Gfi Kitchen, Living Lights 1, Living Lights 2, Living Outlets 1, Living Outlets 2, Dining Lights, Dining Outlets, Den Lights, Den Outlets, Bath 1 Gfi, Bath 1 Outlets, Bath 1 Lights, Bath 2 Gfi, Bath 2 Outlets, Bath 2 Lights, Bath 3 Gfi, Bath 3 Outlets, Bath 3 Lights, Bedr'm 1 Lights, Bedr'm 1 Outlets, Bedr'm 2 Lights, Bedr'm 2 Outlets, Bedr'm 3 Lights, Bedr'm 3 Outlets, Bedr'm 4 Lights, Bedr'm 4 Outlets, Bedr'm 5 Lights, Bedr'm 5 Outlets, Rec Lights, Rec Outlets, Patio Lights, Patio Outlets, Heating 1, Heating 2, Air Cond 1, Air Cond 2, Water Heater 1, Water Heater 2, Washer, Dryer, Outside Outlets, Attic Lights, Attic Outlets, Basem't Lights, Basem't Outlets, Utility Lights, Utility Outlets, Driveway Lights, Pool Gfi, Pool Lights, Pool Heating, Shed Lights, Shed Outlets, Entry Lights, Entry Outlets, Garage Lights, Garage Outlets, Sunr'm Lights, Sunr'm Outlets.

3M™ ScotchCode™ Write-On Wire Marker Book SWB

The 3M™ ScotchCode™ Write-On Wire Marker Book SWB contains self-laminating, write-on markers designed for small volume applications involving special or complex legends that are hand written at the job site.




Specifications and Ordering Information for 3M™ ScotchCode™ Write-On Wire Marker Books SWB

Product Number	UPC (054007-)	Labels Per Book	Write-On Area		Marker Size		Recommended Wire O.D.	Inner Unit Pack	Case Qty.
			A	B	A	C			
SWB-01	49904	180	0.5" (13 mm)	0.5" (13 mm)	0.5" (13 mm)	1.5" (38 mm)	0.16 × 0.31 (4 × 8 mm)	1/bag	5
SWB-02	49905	120	0.75" (19 mm)	0.75" (19 mm)	0.75" (19 mm)	1.75" (44 mm)	0.24 × 0.31 (6 × 8 mm)	1/bag	5
SWB-03	49906	60	1.0" (25 mm)	1.0" (25 mm)	1.0" (25 mm)	2.85" (72 mm)	0.32 × 0.58 (8 × 15 mm)	1/bag	5
SWB-04	49907	30	1.0" (25 mm)	1.0" (25 mm)	1.0" (25 mm)	5.0" (127 mm)	0.32 × 1.55 (8 × 39 mm)	1/bag	5

3M™ ScotchCode™ Marker Pen SMP

3M ScotchCode Marking Pen SMP is suggested for use with ScotchCode write-on products. The pen performs well on nonporous surfaces, has an extra-fine point with permanent, quick-drying ink and is available in black.



Specifications and Ordering Information for 3M™ ScotchCode™ Marker Pen SMP

Product Number	UPC (051128-)	Ink Color	Inner Unit Pack	Case Qty.
SMP	57743	Black	10/box	50



3M and ScotchCode are trademarks of 3M Company.

The 3M products associated with “Made in U.S.A.” statements on this flyer are manufactured in the USA unless stated otherwise.

Important Notice

Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use.

Warranty; Limited Remedy; Limited Liability.

3M’s product warranty is stated in its Product Literature available upon request. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M’s option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any direct, indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



Electrical Markets Division

6801 River Place Blvd.
Austin, TX 78726-9000 USA

Phone 1-800-245-3573
Fax 1-800-245-0329
Web 3M.com/electrical

© 3M 2016. All rights reserved.
80-6109-4242-9B DC