



Chemical protection

ULTRANITRIL 480

Prolonged contact (or immersion) | short wear

Ultra-long chemical protection



CHEMICAL PROTECTION
TYPE A

EN388



4102X

EN ISO 374-1



TYPE A
AJKOPT

EN ISO 374-5



DEXTERITY

EN420:
5/5

CATEGORY 3



0334



ISO 18889



SPECIFIC ADVANTAGES



Durability

- Longer service life: excellent mechanical resistance (abrasion, perforation)



Productivity

- Good grip on slippery objects, due to the embossed texture



Skin protection

- Excellent protection during intensive handling of high-risk chemical products



Guaranteed quality

- Silicone free to prevent traces, defects on metal sheet and glass prior to painting

INDUSTRIES

- Automotive/mechanical industry
- Chemical industry
- Other industries
- Agriculture sector

APPLICATIONS

- Spray mixtures preparation
- Tank filling
- Application & spreading of pesticides
- Pesticides waste management
- Treatment equipment cleaning
- Handling drums of chemical products
- Application of pesticides
- Cleaning of printing-press rollers
- Maintenance
- Timber treatment and finishing



Chemical protection

ULTRANITRIL 480

Prolonged contact (or immersion) | short wear

LEGENDS

EN388

MECHANICAL HAZARDS

PERFORMANCE LEVELS (X = NOT TESTED)

4 1 0 2 X

0-4 0-5 0-4 0-4 A-F P

Impact protection (optional)

Cut resistance according to ISO 13997

Puncture resistance

Tear resistance

Blade cut resistance

Abrasion resistance

EN ISO 374-1

CHEMICAL RISKS

A: Methanol

J: n-Heptane

K: Sodium hydroxide 40%

O: Ammonia 25%

P: Hydrogen peroxide 30%

T: Formaldehyde 37%

TYPE A

ISO 18889

PROTECTION FROM PESTICIDES

G2: Diluted & concentrated pesticides / Mechanical risk

EN ISO 374-5

MICRO-ORGANISMS

Protection against bacteria and fungi

FOOD CONTACT

French decree of 05/08/2020

PRODUCT DETAILS

Interior finish	Chlorinated
Exterior finish	Embossed texture
Material	Nitrile
Cuff characteristic	Straight cuff
Colour.s	Green
Length (cm)	46
Thickness (mm)	0.55
European sizes	7 8 9 10 11

LOGISTIC DETAILS

Packaging	1 pair/bag 12 pairs/carton
-----------	-------------------------------

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/16206/18/1069
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE
- Quality assurance certificat: 0334 - Asqual 14 rue des Reculettes -75013 Paris - France