




TruSound USB-C Headset

PN: 30198


The Verbatim TruSound USB-C Headset delivers clear, balanced audio for smartphones, tablets, laptops, and other modern devices. Its built-in microphone ensures crisp voice pickup for calls and meetings, while cushioned ear pads and an adjustable headband provide all-day comfort. Lightweight yet durable, it stands up to everyday use with ABS plastic and PU leather materials.

In-line controls allow quick access to playback and call functions, making it a convenient companion for work, classes, or entertainment. Designed for versatility, the TruSound Headset offers reliable performance and a comfortable listening experience throughout your daily digital life today.

- USB-C connectivity for effortless plug-and-play use
- High-quality audio performance for music, videos, and calls
- Comfortable on-ear design with soft padded ear cups
- Adjustable headband for a personalised fit
- Integrated in-line controls for managing calls and media
- Built-in microphone for clear voice transmission
- Durable, lightweight construction for everyday use
- Suitable for remote work, online learning, gaming, and entertainment
- 40 mm drive unit for balanced, immersive sound
- 1.5 m USB-C cable



Inline
Microphone



Over-ear
Design



USB-C cable
1.5 m



PN: 30198

Specifications

- Material: ABS plastic / PU leather
- Colour: Black
- Plug: USB-C
- TV Compatibility: Yes, if TV supports USB-C
- Voltage Range: 1.5~6V
- Rated Power: 20 mW
- Max. current: 500 mA
- Cable length: 1500±50 mm
- Drive unit: 40 mm
- Impedance: 32ohm +/- 15
- Frequency Response: 20 Hz~20 KHz
- Sensitivity: 94±3dB @ 1KHZ
- Max Power Input: 50 mW

Storage and Operating Conditions

- Operating Temperature: 0°C ~ +40°C
- Storage Temperature: -20°C ~ +60°C
- Operating Humidity: 0% ~ 95% RH


Pack Contents

- Verbatim TruSound Headset with USB-C
- QSG

Languages

Front of pack: English

Back of pack: English; French; German; Dutch; Italian;
Spanish; Portuguese; Polish; Russian; Czech; Hungarian;
Slovakian; Croatian; Serbian; Romanian; Turkish;
Traditional Chinese; Simplified Chinese; Korean; Japanese



Quick Installation Languages

English, German, French, Traditional Chinese
Support text: English, French, German, Dutch, Italian,
Spanish, Portuguese, Polish, Russian, Czech, Hungarian,
Croatian, Serbian, Slovakian, Romanian, Turkish,
Traditional Chinese, Simplified Chinese, Korean, Japanese

Reorder No.	Description	Tariff code	Barcode	EAN-128	EAN-14
30198	Verbatim TruSound Headset with USB-C	85183000	023942301981	(02)00023942301981(37)10(91)861 (02)00023942301981(37)20(91)861	20023942301985 50023942301986

Reorder No.	
Product Dimensions L x W x H	170 x 80 x 185 mm
Product Weight	200.9 g
Units per Pack	1
Pack Dimensions L x W x H	170 x 80 x 225 mm
Pack Weight	284 g
Units per Inner Carton	10
Inner Carton Dimensions L x W x H	415 x 350 x 235 mm
Inner Carton Weight	3300 g
Units per Outer Carton	20
Outer Carton Dimensions L x W x H	430 x 370 x 490 mm
Outer Cartons Weight	7220 g
Outer Cartons per Layer	6
Layers per Pallet	2
Units per Pallet	240