Product information

10.8V Rotary Hammer BL 16MM CXT

Satisfying the professional's needs

HR166DSMJ

Battery Type	Lithium-ion
Voltage	10.8 v
Battery quantity (4.0Ah)	2
Capacity in Concrete	16 mm
Capacity in Steel	10 mm
Capacity in Wood	13 mm
Impact energy	1.1 J
Impacts per minute	0 - 4800 ipm
Noise sound pressure	86 dB(A)
Noise sound power	97 dB(A)
Noise K factor	3 dB(A)
No Load Speed	0 - 680 rpm
Vibration K factor	1.5 m/sec²
Vibration: Hammer Drilling	7.5 m/sec²
Vibration: Drilling into metal	2.5 m/sec²
Net weight	1.8 - 2.4 kg

STANDARD EQUIPMENT: 197402-0 BL1040B, 821550-0 MAKPAC CONNECTOR CASE (TYPE 2), DC10SA 10.8v Fast charger, Side handle, Depth stop

- Brushless motor
- One touch sliding chuck for easy bit installation and removal.
- 2-mode operation: Rotary only and Rotary hammer
- Electric brake
- Variable speed control by trigger
- Constant speed control
- Forward/reverse rotation
- LED job light
- Compact and lightweight design
- Vibration absorbing housing.

Details correct as of: 25-5-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.