SAUTER **TVO 500N500S-LD**

Practical set for force-displacement-measurements in laboratory and industry

Category

Brand	Sauter
Product category	Test bench
Product group	Test stand set
Product family	TVO-LD

Measuring System

Measurable length [Max]	30 cm
Length measuring device	Length measuring device with data interface

Display

Display type	LED segments
Display type	7 segment LED
Display digit height - smallest digit	9 mm

Construction

Dimension (W×D×H)	570×428×236 mm
Dimension housing (W×D×H)	570×428×236 mm
Dimensions completely mounted (W×D×H)	570×428×236 mm
Material housing	metal, lacquered
Material display housing	metal
Type of drive	Stepper motor
Mounting - force dissipation	5 × threaded hole M6
Mounting - force application	5 × threaded hole M6
Generated force [Max]	500 N
Transversal movement speed [Min]	1 mm/min
Transversal movement speed [Max]	500 mm/min
Transversal movement speed variation	0,5%
Measurement alignment	vertical
Traverse distance [Max]	270 mm

Functions

Speed display	✓
Repeat function	✓
Length measuring - zero setting	✓
Limit switch	✓

Power Supply

Supplied power supply	Power supply unit
Power supply type	Built-in power supply
Plug-in power supply / adapter for countries - optional	EURO UK CH
Input voltage power supply / power [Max]	230 V AC, 50 Hz
Power supply cable removable	removable
Input voltage device / power [Max]	230 V AC, 50 Hz
Power socket for mains adapter	Power supply cable

Environmental conditions

Ambient temperature [Min]	10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓

Packing & Shipping

Delivery time	2 d
Dimensions packaging (W×D×H)	500×400×710 mm
Shipping method	Freight
Net weight approx.	30 kg
Gross weight approx.	40 kg
Shipping weight	40 kg
Shipping volume weight	28,4 kg

Product information

GTIN/EAN number	4045761363052
Trade number	90249000
REACH classification	no prohibited substances

SAUTER **TVO 500N500S-LD**

Practical set for force-displacement-measurements in laboratory and industry

Pictograms

STANDARD