



LENOX® SNAP-BACK™ QUICK CHANGE ARBORS

TOOL-FREE BIT CHANGE

No allen key required to change LENOX® pilot bit*.

ANTI-JAM COLLAR

Reinforced collar drives hole saw without jamming or disengaging.

50% FEWER BREAKS*

Patent pending step bit design for less hole saw grabbing resulting in fewer pilot breaks.

UNIVERSAL HOLE SAW COMPATIBILITY

Accepts all threaded hole saws, no adapters required†.



* Only applies to LENOX® Pilot Drills

** vs previous generation LENOX® Pilot Drill drilling low carbon steel

† For the Range of Diameters Listed On Packaging



STEP 1

Unlock Hole Saw

STEP 2

Unlock Pilot Bit



PROD NO	DESCRIPTION	COMPATIBLE HOLE SAW SIZES		SHANK SIZE	
		IN	MM	IN	MM
LXAH9912PBM	2L QC WITH STEP BIT PILOT DRILL	1-1/4" - 6"	31.8 - 152.4	1/2"	12.7
LXAH9938PBM	5L QC WITH STEP BIT PILOT DRILL	9/16" - 1-3/16"	14.3 - 30.2	3/8"	9.5
LXAH9912CPBM	2L QC WITH CARBIDE & SELF-FEED PILOT DRILL	1-1/4" - 6-1/4"	31.8 - 158.8	1/2"	12.7

LENOX® PILOT DRILLS

UP TO 50% FEWER BREAKS*

Patent pending step bit design for less hole saw grabbing resulting in fewer pilot bit breaks.

REDUCES NEED FOR PRE-DRILLING

Drill holes in metal without slamming due to patent pending design.

ACCURATE STARTS

Precise PILOT POINT® tip starts drilling on contact.

UNIVERSAL COMPATIBILITY**

Fits both quick change and traditional non-quick change arbors.

* vs Previous generation LENOX® Bi-Metal Hole Saw drilling low carbon steel.
** Excluding proprietary arbor systems not using standard 1/4" shank pilot drills.



PROD NO	DESCRIPTION	LENGTH		DIAMETER		COMPATIBLE		PACK SIZE	STEPPED DESIGN	APPLICATION
		IN	MM	IN	MM	SNAP-BACK™ ARBORS	TRADITIONAL ARBORS			
LXAH99314SPB	3-7/16" (87MM) PILOT DRILL 1PK	3-7/16"	87.3	1/4"	6.4	2L QC, 5L QC	1L, 2L, 3L, 4L, 5L, 6L	1	●	
LXAH99314SPB25	3-7/16" (87MM) PILOT DRILL 25PK	3-7/16"	87.3	1/4"	6.4			25	●	
LXAH99414SPB	4-1/4" (108MM) PILOT DRILL 1PK	4-1/4"	108.0	1/4"	6.4			1	●	
LXAH99414SPB25	4-1/4" (108MM) PILOT DRILL 25PK	4-1/4"	108.0	1/4"	6.4			25	●	
LXAH99314CTPB†	3-1/4" (83MM) CARBIDE PILOT DRILL 1PK	3-1/4"	82.6	1/4"	6.4			1	—	
LXAH9334MMPB†	3-3/4" (95MM) CARBIDE PILOT DRILL 1PK	3-3/4"	95.3	1/4"	6.4			1	—	
LXAH99414CTPB†	4-1/4" (108MM) CARBIDE PILOT DRILL 1PK	4-1/4"	108.0	1/4"	6.4			1	—	
LXAH9334SPB†	3-3/4" (95MM) SELF-FEED PILOT DRILL 1PK	3-3/4"	95.3	3/8"	9.5			1	—	

†Does Not Feature Step Bit Design

