KERN **KFP 150V30SM**

Platform: entirely out of stainless steel

Category

Brand	KERN
Product category	Component
Product group	Platform
Product family	KFP-V30-IP67

Measuring System

Weighing capacity [Max]	150 kg
Readability [d]	10 g
Minimum weight [Min] (verifiable)	1 kg
Load cell connection	6-wire
Load cell OIML class	C3
Loadcell type	stainless steel IP67 silicone-coated

Construction

Dimensions weighing surface (W×D)	400×300 mm
Dimensions weighing surface	400×300 mm
Dimensions weighing platform (W×D×H)	400×300×111 mm
Material weighing plate	stainless steel
Material platform	stainless steel
Material load cell(s)	stainless steel
Material substructure	stainless steel
Levelling feet adjustable	✓
Cable length	3 m
Allowed cable length display device [Max]	20 m
Platform Construction	Single-Cell
Load cells - number	1

Functions

IP protection - load cell	IP67

Approval

Conformity assessment possible ex works	✓
Verification scale interval [e]	50 g

Services (optional)

Article number for conformity assessment	965-229
Article number for DAkkS calibration	963-129

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	796×465×226 mm
Shipping method	Parcel service
Net weight approx.	10 kg
Gross weight approx.	12 kg
Shipping weight	16,7 kg
Shipping volume weight	16,7 kg

Product information

GTIN/EAN number	4045761250017
Trade number	90318080
REACH classification	no prohibited substances

Pictograms

STANDARD

FACTORY