MB168B PORTABLE USB-POWERED MONITOR

Two Screens Are Better Than One

Metallic Spun Finish Design

ASUS Smart Case

One Cable Does the Job

■ Key Features ■

USB 3.0 Monitor

Single USB3.0 connection for video transmission and power supply

Ultra Slim

Slim and stylish, only 8mm/ 0.3inch in thickness

LED Backlight

Green in mind with mercury-free LED-backlight panel

Ultra-light Weight

Lightweight design, only 800g/ 1.76 pounds in weight

Auto Rotate

Instant rotate screen direction from portrait to landscape, or vice versa

Ergo Case

ASUS Smart Case included, featured as angle-adjustable stand

AI Light

Automatically adjust display brightness level by detecting ambient lighting

green

Low power consumption when in operation and no power consumption in stand-by mode

■ Specification ■

Display	Panel Size: Wide Screen 15.6"(39.6cm) 16:9 True Resolution : 1366x768 Pixel Pitch : 0.252mm Brightness(Max) : 200 cd/㎡ Contrast Ratio (Max) :500:1 Viewing Angle (CR≧10) : 90°(H)/65°(V) Response Time : 11ms
Convenient Hotkey	Power Button Brightness Adjustment
I/O Ports	Signal Input : USB3.0
Power Consumption	Power ON : < 5W Power Saving Mode : 0W Power Off Mode : 0W
Mechanical Design	Chassis Colors : Black+ Silver
Dimensions	Phys. Dimension with Stand(WxHxD) : 379x236x8mm Box Dimension (WxHxD) :435x297x57mm
Weight	Net Weight (Esti.) : 0.8kg Gross Weight (Esti.) : 2.0kg
Warranty	3-year System Warranty, 3-year Panel Warranty (in Specific Countries), Free Service Hotlines (in Specific Countries), Free Pick-up Service (in Specific Countries)
Miscellaneous	Auto-Rotate, AI Light
Accessories	Support CD (MB168 Driver for Microsoft Windows operating system, MB168 Driver for Apple OS X operating system, ASUS EzLink Utility) USB 3.0 Cable Quick Start Guide ASUS Smart Case
Regulation Approval	UL/cUL, CB, CE, CCC, FCC, BSMI, EAC, C-Tick, VCCI, RoHS, WEEE, Windows 7 & Windows 8 WHQL, PSE

***All specifications are subject to change without notice.*