



## PRODUCT NUMBER: 2232273 POLYTRIL™ AIR COMFORT

Light handling, assembling in oily environment. Handling in wet and greasy environment. Assembly work, plumbing, joinery, construction, automotive industry, white and brown goods.

# Honeywell

### Overview

**Reference Number**

2232273

**Product Type**

Gloves

**Range**

General purpose

**Line**

Light & medium handling

**Brand**

Honeywell

**Brand formerly known as**

SPERIAN

**Industry**

- Industry
- Automotive and Part Manufacturer
- Maintenance
- Offshore
- Transportation
- Utilities

**Product Use**

Light handling, assembling in oily environment. Handling in wet and greasy environment. Assembly work, plumbing, joinery, construction, automotive industry, white and brown goods.

### Features & Benefits

**Feature**

Polyamide/Cotton/Elasthane knitted glove  
Black foam nitrile on the palm and fingers  
Open back  
Elasticated knitted wrist

**Benefit**

COMFORT

The ergonomic seamless knit construction conforms better to the natural shape of the hand for greater strength and durability.

The Lycra® yarn gives a better tactile sensitivity for the assembling of small parts.  
 The addition of cotton increases the absorption of perspiration and comfort.  
 Nitrile foam coating and open back provide superior ventilation of the hand.  
 The liner combining polyamide/cotton/elasthane avoids skin contact with the coating and helps keeping hands cool and dry.

**RESISTANCE**

The nitrile coating provides oil and abrasion resistance and breathability.  
 The foam version of nitrile helps improving the grip in wet and oily environments.

**HYGIENE**

Black colour suitable for dirty applications and environments.

**Technical Description**

**Description**

CE CATEGORY : II Intermediary risks  
 In accordance with standards :  
 EN 420-03 Basic standards  
 EN 388-16 Mechanical hazards

**CHARACTERISTICS :**

Polyamide/Cotton/Lycra® knitted glove  
 Black foam nitrile coating on the palm and fingers  
 Open back  
 Elasticated knitted wrist

**Product Technology**

Knitted Coated

**Gauge**

13

**Glove/liner color**

Black

**Coating Type**

Polyamide, coton et lycra®

**Length**

24,5 cm

**Harmlessness**

In conformity with the European standards.

**Dexterity**

Class 5

**Sizes**

6 à 11

**EN 388 - Mechanical Hazards Abrasion Resistance**

Abrasion resistance	3
Cutting resistance (Coupe test)	1
Tear resistance	2
Puncture resistance	1
Cutting resistance (TDM test)	X

**Certifications**

**EC Category PPE**

2

**Quality Assurance**

ISO 9001 / 2000

**EC Certificate Number**  
0075/797/162/05/18/0795

**EC Attestation**  
CE Certificate

**EC Attestation Number**  
0075/797/162/05/18/0795

## Additional Information

**User Manual**  
UI 202

## Maintenance

**Storage Information**  
Minimum packaging : 10 pairs.  
Cartons of 100 pairs.

**Care Instructions**  
This article can be cleaned. For cleaning instructions, contact Honeywell Safety Products.