Your Expert Partner for **Human Machine Interfaces**

Rugged keypads complete, 8PB

K09-00.000034

https://www.eao.com/component/K09-00.000034/e...

Your product:

K09-00.000034
Rugged keypads complete, 8PB

PRODUCT RANGE

Type of module:	8 Push buttons
Product variant:	SUPER (CAN, RGB LED)

FRONT

Front form:	Rectangular

MOUNTING

Design:	Flush
Mounting cut-out:	142.64 mm x 68.8 mm
Mounting type:	Clip in & screw in

OPERATING-/INDICATION PART

Halo ring illumination:	RGB
Symbol:	No Symbol
Marking symbol colour:	White

ELECTRICAL CHARACTERISTICS

Operating voltage:	8 - 32 V DC
Load Dump Protection:	A / B
Communication interface:	J1939

MECHANICAL CHARACTERISTICS

Terminal:	Deutsch DT04-6P
Mechanical lifetime:	2 Mil. cycles of operation
Operating force:	11 N
Weight:	0.339 kg

AMBIENT CONDITION

IP Protection:	IP6K9K
Operating temperature:	– 40 °C ... + 85 °C
Storage temperature:	– 40 °C ... + 85 °C

CERTIFICATE

Approbations:	E1, ECE R10, ECE R118
Conformities:	CE
REACH:	REACH compliant
RoHS:	RoHS compliant

OTHER

Short Description:	Rugged keypads complete, 8PB, 8 - 32 V DC, Deutsch DT04-6P, Rectangular, No Symbol, SUPER (CAN, RGB LED)
Dimension:	150.56 mm x 76.55 mm x 36.8 mm
Housing colour:	Black
Product attributes:	Illumination features: steady lighting, flashing, pulses, rotations, colour changes