

Features

- Precise temperature control
- Rapid warming
- Auto sleep
- Temperature lock
- °C / °F switch
- Auto standby
- LED indicator

RS PRO Soldering Station 60W, 230V, 100-500°C

RS Stock No.: 0631067



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range

has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RRS PRO Digital Soldering Station

It is a highly versatile tool that caters to both DIY enthusiasts and professionals. Its user-friendly design and intuitive control panel make it accessible even for beginners. With its rapid heat-up time and adjustable temperature control, it is well-suited for a wide range of soldering tasks. The LED indicator provides convenient status monitoring, while the inclusion of a pure copper transformer and high-quality ceramic heating element ensures efficient heat transfer. Whether you're a hobbyist or a seasoned professional, it is a reliable and efficient choice.

Features and Benefits

- Fast heat-up time for quick use
- LED indicator for easy status monitoring
- Pure copper transformer for efficient heat transfer
- Wide temperature range for versatile soldering applications

General Specifications

| | |
|---------------------------|--|
| Plug Type | Type G – British 3-pin; Type E (France-2 round pins + hole for ground) |
| Tasks Supported | Soldering |
| Wattage | 60 W |
| Input Voltage | 230 V |
| Soldering Tip Temperature | 100-500 °C |
| Number of Outputs | 1 |
| Display Type | LED |
| ESD Safe | No |

Approvals

| | |
|---------------|----------------|
| Declarations | REACH DoC |
| Standards Met | CE, UKCA, RoHS |

Similar Products

| Stock No. | Brand | Product Name | Wattage | Tasks Support | Plug Type |
|-----------|-----------|-------------------|---------|-------------------------|--------------------|
| 0631067 | RS PRO | Soldering Station | 60W | Desoldering / Soldering | Type G & Type E |
| 0631068 | RS PRO | Soldering Station | 80W | Desoldering / Soldering | Type G & Type E |
| 0631069 | RS PRO | Soldering Station | 70W | Desoldering / Soldering | Type G & Type E |
| 0631071 | RS PRO | Soldering Station | 80W | Desoldering / Soldering | Type G & Type E |
| 0631072 | RS PRO | Soldering Station | 60W | Desoldering / Soldering | Type G & Type E |
| 0631066 | RS PRO | Soldering Iron | 90W | Desoldering / Soldering | Type G & Type E |

Soldering Iron

| Stock No. | Brand | Product Name | Power Type | Wattage | Voltage | Temperature Range |
|-----------|-------|--------------|------------|---------|---------|-------------------|
|-----------|-------|--------------|------------|---------|---------|-------------------|

| | | | | | | |
|---------|-----------|----------------|----------|-----|-----------------|------------|
| 0631077 | RS PRO | Soldering Iron | Electric | 60W | AC 25V (MAX) | 100-500 °C |
|---------|-----------|----------------|----------|-----|-----------------|------------|

Soldering Tips

| Stock No. | Brand | Product Name | Tip Shape | Tip Size | Tip Angle |
|-----------|--------|----------------|------------------|----------|-----------|
| 2024516 | RS PRO | Soldering Tips | Straight Chisel | 1.6 mm | 0° |
| 2024517 | RS PRO | Soldering Tips | Straight Hoof | 0.5 mm | 45° |
| 2024518 | RS PRO | Soldering Tips | Straight Hoof | 0.8 mm | 45° |
| 2024520 | RS PRO | Soldering Tips | Straight Hoof | 1 mm | 60° |
| 2024521 | RS PRO | Soldering Tips | Straight Conical | 0.2 mm | 0° |
| 2024522 | RS PRO | Soldering Tips | Straight Conical | 0.2 mm | 0° |
| 2024523 | RS PRO | Soldering Tips | Straight Conical | 0.5 mm | 0° |
| 2024524 | RS PRO | Soldering Tips | Straight Knife | 2 mm | 45° |
| 2024526 | RS PRO | Soldering Tips | Straight Knife | 1.6 mm | 45° |
| 2024527 | RS PRO | Soldering Tips | Straight Conical | 0.2 mm | 0° |
| 2024528 | RS PRO | Soldering Tips | Straight Hoof | 3 mm | 45° |
| 2024529 | RS PRO | Soldering Tips | Straight Hoof | 4 mm | 45° |
| 2024530 | RS PRO | Soldering Tips | Bent Conical | 0.2 mm | 153° |
| 2024532 | RS PRO | Soldering Tips | Straight Knife | 2 mm | 45° |
| 2024533 | RS PRO | Soldering Tips | Bent Conical | 0.5 mm | 153° |
| Stock No. | Brand | Product Name | Tip Shape | Tip Size | Tip Angle |
| 7998973 | RS PRO | Soldering Tips | Conical Chisel | 2.4 mm | 0° |
| 7998976 | RS PRO | Soldering Tips | Conical Sharp | 0.2 mm | 0° |
| 7998979 | RS PRO | Soldering Tips | Conical Chisel | 1.2 mm | 0° |
| 7998982 | RS PRO | Soldering Tips | Conical Chisel | 3.2 mm | 0° |
| 7998985 | RS PRO | Soldering Tips | Straight Conical | 0.8 mm | 0° |
| 7998989 | RS PRO | Soldering Tips | Conical Bevel | 2 mm | 45° |


Accessory

| Stock No. | Brand | Product Name | Material | For Use With |
|-----------|-----------|------------------------|-----------------------------------|---------------------------------------|
| 136-8299 | RS PRO | Solder Tip Cleaner kit | Plastic holder with brass wool | Gentle Fine Clean of Soldering Tip |

Soldering Stations




| | | | | |
|----------|-----------|--|------------|---|
| 136-8300 | RS PRO | Brass Wool for solder Tip Clean | Brass Wool | Gentle Fine Clean of Soldering Tip (1368299, 0631071, 0631069, 0631068) |
| 0631073 | RS PRO | Soldering Iron Cleaning Sponge (PK of 5) | N/A | 0631068, 0631067, 0631072 |




Main unit



Soldering Iron



Iron stand



Sponge