Rittal – The System.

Faster – better – everywhere.

PSM socket modules – DK 7856.080

Date : Apr 26, 2021

ENCLOSURES POWER DISTRIBUTION CLIMATE CONTROL IT INFRASTRUCTURE SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

PSM socket modules – DK 7856.080

created: 26.04.2021 build on www.rittal.com/uk-en

Product description

Design:	non-switchable
Description:	The modular system facilitates basic configuration of the racks, thanks to a vertical support rail with single-/3-phase infeed. The various socket modules to supply the active components may be snap-fitted into the support rail. The various modules, earthing pins, IEC320 etc. may be inserted into the support rail in any combination. This is easily achieved, even by non-electricians, thanks to the shock hazard protected plug & play system.
Material:	Section: Aluminium, anodised Socket inserts: Plastic (PA6 GF 30 V1)

Product description

Sockets:	6 x IEC 320 socket C13 - Black
Required number of module slots:	1
Dimensions:	Length: 250 mm
Infeeds:	Phases per infeed: 1~
Type of electrical connection:	WAGO WINSTA MIDI
Thermal overcurrent protection:	–
Packs of:	1 pc(s).
Weight/pack:	0.33 kg

Â© Rittal 2021

Copper weight (kg per piece):	0
EAN:	4028177402539
Customs tariff number:	85369001
ETIM 7.0:	EC000330
ETIM 6.0:	EC000330
eCl@ss 8.0/8.1:	27142604
eCl@ss 6.0/6.1:	27142604
Product description:	DK PSM Plus socket module, C13, 6-way, black, non-switchable

Approvals

Approvals:	UR + C-UR
Certificates:	EAC
Declarations:	Declaration of conformity