

Cable tie - WT-UV HF 4,5X200 BK - 3240834

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Cable binders for quick and permanent fastening, UV-resistant and weatherproof (ISO 4892_QUV-B 600 h)

Why buy this product



Key commercial data

| | |
|--------------------------------------|---|
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| GTIN |  4 046356 705820 |
| Weight per Piece (excluding packing) | 1.44 g |
| Custom tariff number | 39269097 |
| Country of origin | Croatia |

Technical data

Dimensions

| | |
|------------|--------|
| Length (b) | 200 mm |
| Width (a) | 4.8 mm |

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 105 °C |
| Ambient temperature (assembly) | -10 °C ... 60 °C |
| Optimum ambient temperature (storage/transport) | 23 °C 50 % Polyamide 6.6 has pronounced hygroscopic properties. It absorbs or releases water in accordance with the level of humidity within its environment. Its properties are ideal when the percentage of water is 2 - 3%. The packaging, which is tailored specifically to the product concerned, contains the optimum level of moisture. To ensure that the ideal properties are maintained, the following points should be observed during storage: Keep product stored inside sealed original packaging, carry out any product processing soon after breaking open the packaging, avoid direct sunlight, avoid direct heat. |

General

Cable tie - WT-UV HF 4,5X200 BK - 3240834

Technical data

General

| | |
|---|--------------------------------|
| Color | black |
| Type | Internal teeth |
| Components | free from silicone and halogen |
| Inflammability class according to UL 94 | V2 |
| Material | PA 6.6 |
| RoHS compliant | Yes |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27140702 |
| eCl@ss 4.1 | 27140702 |
| eCl@ss 5.0 | 27140702 |
| eCl@ss 5.1 | 27140702 |
| eCl@ss 6.0 | 27140702 |
| eCl@ss 7.0 | 27140702 |
| eCl@ss 8.0 | 27140702 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC000046 |
| ETIM 4.0 | EC000046 |
| ETIM 5.0 | EC000046 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30212109 |
| UNSPSC 7.0901 | 27121703 |
| UNSPSC 11 | 27121703 |
| UNSPSC 12.01 | 27121703 |
| UNSPSC 13.2 | 27121703 |

Accessories

Accessories

Universal tools

Cable tie tool - UNIFOX-CT 4,8 - 1212475



Cable binder pliers, for plastic cable binders with a width of 2.2 - 4.8 mm, for a material thickness of up to 1.6 mm

Cable tie - WT-UV HF 4,5X200 BK - 3240834

Accessories

Cable tie tool - UNIFOX-CT 4,8P - 1212609



Cable binder pliers, for plastic cable binders with a width of 2.2 - 4.8 mm, for a material thickness of up to 1.6 mm

Phoenix Contact 2015 © - all rights reserved
<http://www.phoenixcontact.com>