KERN **FPE 3K-4**

Entry-level bench scale with stainless steel weighing plate and checkweighing function

Category

Brand	KERN
Product category	Industrial scale
Product group	Bench scale
Product family	FPE

Measuring System

Weighing system	Strain gauge
Number of weighing ranges	1
Weighing capacity [Max]	3000 g
Readability [d]	0,2 g
Reproducibility	0,2 g
Linearity	± 0,6 g
Resolution	15.000
Tare range	3000 g
Adjustment options	Adjusting with external weight
Recommended adjusting weight	3 kg (M1)
Possible calibration points	3 kg
Stabilization time	2 s
Eccentric loading at 1/3 [Max]	1 g
Construction type of the scale	Single-range balance
Units	kg g lb oz PCS tJ lb:oz
Units (if device is conformity assessed)	kg g
Load cell connection	4-wire
Maximum creep (15 minutes)	800 mg
Maximum creep (30 minutes)	1,6 g
Default unit	g
Loadcell type	ZEMIC L6D

Display

Display type	LCD
Display backlight	✓
Display screen size	100×35 mm
Display segments	7
Display digit height	25 mm
Languages of the user interface	English

Construction

Dimension housing (W×D×H)	288×233×102 mm
Dimensions completely mounted (W×D×H)	288×233×102 mm
Dimensions weighing surface (W×D)	190×230 mm
Dimensions weighing surface	190×230 mm
Dimensions weighing platform (W×D×H)	230×190×20 mm
Material housing	stainless steel, plastic
Material weighing plate	stainless steel
Material load cell(s)	aluminium
Level indicator	✓
Levelling feet adjustable	✓

Functions

Tolerance weighing	✓
Tolerance weighing - type of signal	visual
Capacity - Display	✓
Counting function	✓
Counting resolution (laboratory conditions)	15.000
Smallest piece weight when piece counting - laboratory conditions	200 mg
Smallest piece weight when piece counting - normal conditions	2 g
Reference quantity	10, 20, 50, 100, 200
Auto-off interval(s) in battery mode/rechargeable battery mode	selectable
Auto-off interval(s) in mains power mode	selectable
Tare function	manual (multi)
Number of keys for operation	4

Power Supply

Supplied power supply	Power supply unit

KERN **FPE 3K-4**

Entry-level bench scale with stainless steel weighing plate and checkweighing function

Power supply type	USB including power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	EURO
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	5 V, 1 A
Power socket for mains adapter	Hollow plug inside plus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 9,4 mm
Battery / accumulator type	Li-Ion
Rechargeable battery operating time - backlight on	400 h
Rechargeable battery operating time - backlight off	500 h
Rechargeable battery charging time	4 h
Rechargeable battery optional	Rchrg. battery optional

Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Humity of environment [Min]	5 %
Humity of environment [Max]	85 %
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓

Services (optional)

Article number for adjustment at the location of installation	961-247
Article number for DAkkS calibration	963-127
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	340×295×165 mm
Shipping method	Parcel service
Net weight approx.	1,8 kg
Gross weight approx.	2,8 kg
Shipping weight	3,3 kg
Shipping volume weight	3,3 kg

Product information

GTIN/EAN number	4045761488632
Trade number	84238129
REACH classification	no prohibited substances

Pictograms

STANDARD

OPTION